


DIN 46234

NON-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	16	14	12	10	8
AMP.	18	30	35	50	70

TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION mm						CRIMPING TOOL	Q'TY BOX
		d2		d3	l	a	C	d1	S		
16-14 A.W.G. 1.5-2.5 mm ²	DRNB4-2.5	#8	4.3	8.0	12.0	5.0	4.5	2.3	0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:2	1000
	DRNBS5-2.5	#10	5.3		13.5						1000
	DRNB5-2.5	#10	5.3	10.0	14.0						1000
	DRNB6-2.5	1/4	6.5	11.0	16.0						1000
	DRNB8-2.5	5/16	8.4	14.0	17.0						1000
	DRNB10-2.5	3/8	10.5	15.0							1000
	DRNBL10-2.5	3/8	10.5	18.0	18.5						1000
	DRNB12-2.5	1/2	13.0		20.0						1000
12-10 A.W.G. 2.5-6 mm ²	DRNB3-6	#4	3.2	6.0	14.0	6.0	6.0	3.6	1.0	IZUMI MODEL 5N18 WITH DIE INDEX NO:5.5 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:5.5(6.0)	1000
	DRNBL3-6	#4	3.2	7.2							1000
	DRNB3.5-6	#6	3.7	8.0	13.5						1000
	DRNB4-6	#8	4.3		14.0						1000
	DRNB5-6	#10	5.3	10.0	15.0						1000
	DRNB6-6	1/4	6.5	11.0	16.0						1000
	DRNBL6-6	1/4	6.5	18.0	21.0						1000
	DRNB8-6	5/16	8.4	14.0	19.0						1000
	DRNB10-6	3/8	10.5	18.0	21.0						500
	DRNB12-6	1/2	13.0								500
8 A.W.G. 10 mm ²	DRNB4-10	#8	4.3	10.0	16.0	8.0	8.0	4.5	1.1	IZUMI MODEL 5N18 WITH DIE INDEX NO:8 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:8(10)	500
	DRNB5-10	#10	5.3								500
	DRNB6-10	1/4	6.5	11.0	17.0						500
	DRNB8-10	5/16	8.4	14.0	20.0						500
	DRNB10-10	3/8	10.5	18.0	21.0						500
	DRNB12-10	1/2	13.0	22.0	23.0						500

(UL) c(UL) ALL LISTED