

HEAT SHRINKABLE-FULLY FEMALE DISCONNECTORS "HD"(DOUBLE CRIMP TYPE)

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	3	4	7	10	15	20	24


MAXIMUM ELECTRICAL RATING: 300 VOLTS MAX.

SHRINK TEMP.: 150°C OPERATING TEMP.: -40°C~+105°C

INSULATION MATERIAL: HIGH DENSITY PE.

INSULATION MATERIAL: WITH COPPER SLEEVE ON BARREL

TERMINAL MATERIAL: BRASS



WIRE RANGE A.W.G. mm ²	ITEM NO.	NEMA TAB inch mm	W		D		L		INSULATED COLOR	CRIMPING TOOL	QTY BOX
			inch	mm	inch	mm	inch	mm			
22-16 A.W.G. 0.5-1.5 mm ²	FDFHD1-250	.032X.250 0.8X6.35	.260	6.6	.256	6.5	1.102	28.0	RED	K.S. MODEL KST2000A WITH DIE INDEX COLOR:RED	500
16-14 A.W.G. 1.5-2.5 mm ²	FDFHD2-250		.260	6.6	.256	6.5	1.102	28.0	BLUE	K.S. MODEL KST2000A WITH DIE INDEX COLOR:BLUE	500
12-10 A.W.G. 4-6 mm ²	FDFHD5-250		.260	6.6	.295	7.5	1.102	28.0	YELLOW	K.S. MODEL KST2000A WITH DIE INDEX COLOR:YELLOW	500