

VINYL- INSULATED DOUBLE CRIMP RECEPTACLE DISCONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	3	4	7	10	15	20	24

MAXIMUM ELECTRICAL RATING: 75°C 600 VOLTS MAX.

INSULATION MATERIAL: VINYL TERMINAL MATERIAL: BRASS


INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL

TERMINAL BARREL I.D.:

22-16 A.W.G.: C=1.7mm 16-14 A.W.G.: C=2.3mm 12-10 A.W.G.: C=3.4mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION inch mm						CRIMPING TOOL	Q'TY BOX
		W	F	L	B	D	T		
22-16 A.W.G. 0.5-1.5 mm ²	FRD1-156	.154 3.9	.276 7.0	.917 23.3	.413 10.5	.157 4.0	.016 0.4	IZUMI MODEL 34 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:RED	1000
16-14 A.W.G. 1.5-2.5 mm ²	FRD2-156	.154 3.9	.276 7.0	.917 23.3	.413 10.5	.185 4.7	.016 0.4	IZUMI MODEL 34 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:BLUE	1000
	FRD2-195	.193 4.9							1000
12-10 A.W.G. 4-6 mm ²	FRD5-195	.193 4.9	.276 7.0	.988 25.1	.492 12.5	.244 6.2	.018 0.45	IZUMI MODEL 5 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:YELLOW	500

  ALL LISTED

