

VINYL-INSULATED DOUBLE CRIMP RECEPTACLE DISCONNECTORS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	3	4	7	10	15	20	24

MAXIMUM ELECTRICAL RATING: 75°C 600 VOLTS MAX.
INSULATION MATERIAL: VINYL TERMINAL MATERIAL: BRASS
INSULATION COLOR:

22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■ 12-10 A.W.G.: YELLOW ■
DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL
TERMINAL BARREL I.D.:

22-16 A.W.G.: C=1.7mm 16-14 A.W.G.: C=2.3mm 12-10 A.W.G.: C=3.4mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION inch mm						CRIMPING TOOL	Q'TY BOX
		W	F	L	B	D	T		
22-16 A.W.G. 0.5-1.5 mm ²	FRSD1-156	.154 3.9	.276 7.0	.866 22.0	.413 10.5	.157 4.0	.016 0.4	K.S. MODEL 34 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR: RED	1000
	FRSD1-180	.173 4.4							1000
16-14 A.W.G. 1.5-2.5 mm ²	FRSD2-156	.154 3.9	.276 7.0	.866 22.0	.413 10.5	.185 4.7	.016 0.4	K.S. MODEL 34 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR: BLUE	1000
	FRSD2-180	.173 4.4							1000
	FRSD2-195	.193 4.9							1000
12-10 A.W.G. 4-6 mm ²	FRSD5-195	.193 4.9	.276 7.0	.965 24.5	.512 13.0	.244 6.2	.018 0.45	K.S. MODEL 5 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR: YELLOW	500