

NYLON-INSULATED DOUBLE CRIMP FLANGE SPADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.


INSULATION MATERIAL: NYLON

INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION ^{inch} mm							CRIMPING TOOL	Q'TY BOX															
		d2		W	F	L	E	D	d1	A			T														
22-16 A.W.G. 0.5-1.5 mm ²	FSNYDS1-2	#2	.087 2.2	.252 6.4	.205 5.2							IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000B WITH DIE INDEX COLOR:RED	1000														
	FSNYD1-3.2	#4	.126 3.2	.295 7.5													1000										
	FSNYDS1-3.2	#4	.126 3.2	.252 6.4																		1000					
	FSNYD1-3.7	#6	.146 3.7	.295 7.5																							1000
	FSNYDS1-3.7	#6	.146 3.7	.252 6.4																							
	FSNYDL1-3.7	#6	.146 3.7	.335 8.5	.283 7.2	1.004 25.5								1000													
	FSNYD1-4	#8	.169 4.3	.295 7.5	.201 5.1	.787 20.0								1000													
	FSNYDL1-4	#8	.169 4.3	.335 8.5	.283 7.2	1.004 25.5								1000													
	FSNYD1-5	#10	.209 5.3	.295 7.5	.201 5.1	.787 20.0								1000													
	FSNYDL1-5	#10	.209 5.3	.335 8.5	.283 7.2	1.004 25.5								1000													
16-14 A.W.G. 1.5-2.5 mm ²	FSNYD2-3.7	#6	.146 3.7	.295 7.5	.205 5.2	.807 20.5						IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000B WITH DIE INDEX COLOR:BLUE	1000														
	FSNYDL2-3.7	#6	.146 3.7	.335 8.5	.283 7.2	.945 24.0							1000														
	FSNYD2-4	#8	.169 4.3	.295 7.5	.205 5.2	.807 20.5							1000														
	FSNYDM2-4	#8	.169 4.3	.315 8.0	.268 6.8	.965 24.5							1000														
	FSNYDL2-4	#8	.169 4.3	.335 8.5	.283 7.2	.945 24.0							1000														
	FSNYD2-5	#10	.209 5.3	.295 7.5	.205 5.2	.807 20.5							1000														
	FSNYDL2-5	#10	.209 5.3	.335 8.5	.283 7.2	.945 24.0							1000														
12-10 A.W.G. 4-6 mm ²	FSNYD5-3.7	#6	.146 3.7	.335 8.5	.295 7.5	1.063 27.0						IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000B WITH DIE INDEX COLOR:YELLOW	500														
	FSNYDS5-3.7	#6	.146 3.7	.299 7.6	.244 6.2	1.004 25.5							500														
	FSNYD5-4	#8	.169 4.3	.335 8.5	.295 7.5	1.063 27.0							500														
	FSNYDS5-4	#8	.169 4.3	.299 7.6	.244 6.2	1.004 25.5							500														
	FSNYD5-5	#10	.209 5.3	.335 8.5	.295 7.5	1.063 27.0							500														
	FSNYDS5-5	#10	.209 5.3	.299 7.6	.244 6.2	1.004 25.5							500														