

NYLON-FULLY INSULATED RECEPTACLE DISCONNECTORS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14
AMP.	3	4	7	10	15

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: NYLON **TERMINAL MATERIAL: BRASS**
INSULATION COLOR:

 22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■
TERMINAL BARREL I.D.:

22-16 A.W.G.: C=1.7mm 16-14 A.W.G.: C=2.3mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION ^{inch} mm						CRIMPING TOOL	Q'TY BOX
		W	F	L	B	D	T		
22-16 A.W.G. 0.5-1.5 mm ²	FRFNY1-156	.154 3.9	.276 7.0	.992 25.2	.433 11.0	.157 4.0	.016 0.4	K.S. MODEL KST2000C WITH DIE INDEX COLOR:RED	1000
	FRFNY1-180	.173 4.4							
16-14 A.W.G. 1.5-2.5 mm ²	FRFNY2-156	.154 3.9	.276 7.0	.992 25.2	.433 11.0	.177 4.5	.016 0.4	K.S. MODEL KST2000C WITH DIE INDEX COLOR:BLUE	1000
	FRFNY2-180	.173 4.4							500
	FRFNY2-195	.193 4.9		1.043 26.5					500

NYLON-FULLY INSULATED BULLET DISCONNECTS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14
AMP.	3	4	7	10	15

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: NYLON **TERMINAL MATERIAL: BRASS**
INSULATION COLOR:

 22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■
TERMINAL BARREL I.D.:

22-16 A.W.G.: C=1.7mm 16-14 A.W.G.: C=2.3mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION ^{inch} mm						CRIMPING TOOL	Q'TY BOX
		W	F	L	B	D	T		
22-16 A.W.G. 0.5-1.5 mm ²	MPFNY1-156	.157 4.0	.413 10.5	1.063 27.0	.394 10.0	.157 4.0	.016 0.4	K.S. MODEL KST2000C WITH DIE INDEX COLOR:RED	500
16-14 A.W.G. 1.5-2.5 mm ²	MPFNY2-156	.157 4.0	.413 10.5	1.063 27.0	.394 10.0	.177 4.5	.016 0.4	K.S. MODEL KST2000C WITH DIE INDEX COLOR:BLUE	500

UL cUL ALL LISTED