


NON-INSULATED LIPPED BLADE TERMINALS



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.		DIMENSION inch mm								CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	W	F	L	E	D	d1	A	T		
22-16 A.W.G. 0.5-1.5 mm ²	LBNB1-3	LBN1-3	.118 3.0								IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:22-18 OR K.S. MODEL KM-70L WITH DIE SET NO.DIE-1322 WITH DIE INDEX NO:22-18	1000
	LBNB1-4.6	LBN1-4.6	.181 4.6	.685 17.4	.874 22.2	.189 4.8	.134 3.4	.067 1.7	.083 2.1	.030 0.75		1000
16-14 A.W.G. 1.5-2.5 mm ²	LBNB2-3	LBN2-3	.118 3.0								IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:16-14 OR K.S. MODEL KM-70L WITH DIE SET NO.DIE-1322 WITH DIE INDEX NO:16-14	1000
	LBNB2-4.6	LBN2-4.6	.181 4.6	.685 17.4	.874 22.2	.189 4.8	.161 4.1	.091 2.3	.083 2.1	.031 0.8		1000
12-10 A.W.G. 4-6 mm ²	LBNB5-3	LBN5-3	.118 3.0						.110 2.8		IZUMI MODEL 5N18 WITH DIE INDEX NO:5.5 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:12-10 OR K.S. MODEL KM-70L WITH DIE SET NO.DIE-1322 WITH DIE INDEX NO:12-10	1000
	LBNB5-4.6	LBN5-4.6	.181 4.6	.677 17.2	.913 23.2	.236 6.0	.220 5.6	.134 3.4	.106 2.7	.039 1.0		1000

UL cUL ALL LISTED