


**NON-INSULATED
FLANGE SPADE TERMINALS**



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION <small>inch mm</small>							CRIMPING TOOL	Q'TY BOX										
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	A			T									
22-16 A.W.G. 0.5-1.5 mm ²	FSNBS1-2 [Ⓢ]	FSNS1-2 [Ⓢ]	#2	.087 2.2	.252 6.4	.205 5.2								IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:1.25	1000								
	FSNB1-3.2	FSN1-3.2	#4	.126 3.2	.295 7.5	.201 5.1																1000	
	FSNBS1-3.2	FSNS1-3.2	#4	.126 3.2	.252 6.4																		
	FSNB1-3.7	FSN1-3.7	#6	.146 3.7	.295 7.5																		
	FSNBS1-3.7	FSNS1-3.7	#6	.146 3.7	.252 6.4																		
	FSNBL1-3.7	FSNL1-3.7	#6	.146 3.7	.335 8.5	.283 7.2									.768 19.5	.189 4.8	.134 3.4	.067 1.7	.059 1.5	.030 0.75			
	FSNB1-4	FSN1-4	#8	.169 4.3	.295 7.5	.201 5.1									.551 14.0								
	FSNBL1-4	FSNL1-4	#8	.169 4.3	.335 8.5	.283 7.2									.768 19.5								
	FSNB1-5	FSN1-5	#10	.209 5.3	.295 7.5	.201 5.1									.551 14.0								
	FSNBL1-5	FSNL1-5	#10	.209 5.3	.335 8.5	.283 7.2									.768 19.5								
16-14 A.W.G. 1.5-2.5 mm ²	FSNB2-3.7	FSN2-3.7	#6	.146 3.7	.295 7.5	.205 5.2	.571 14.5							IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:2	1000								
	FSNBL2-3.7	FSNL2-3.7	#6	.146 3.7	.335 8.5	.283 7.2	.709 18.0															1000	
	FSNB2-4	FSN2-4	#8	.169 4.3	.295 7.5	.205 5.2	.571 14.5																
	FSNBM2-4	FSNM2-4	#8	.169 4.3	.315 8.0	.268 6.8	.728 18.5								.189 4.8	.161 4.1	.091 2.3	.059 1.5	.031 0.8		1000		
	FSNBL2-4	FSNL2-4	#8	.169 4.3	.335 8.5	.283 7.2	.709 18.0																1000
	FSNB2-5	FSN2-5	#10	.209 5.3	.295 7.5	.205 5.2	.571 14.5																
	FSNBL2-5	FSNL2-5	#10	.209 5.3	.335 8.5	.283 7.2	.709 18.0																
12-10 A.W.G. 4-6 mm ²	FSNB5-3.7	FSN5-3.7	#6	.146 3.7	.335 8.5	.295 7.5	.787 20.0							IZUMI MODEL 5N18 WITH DIE INDEX NO:5.5 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:5.5						1000			
	FSNBS5-3.7	FSNS5-3.7	#6	.146 3.7	.299 7.6	.244 6.2	.728 18.5															1000	
	FSNB5-4	FSN5-4	#8	.169 4.3	.335 8.5	.295 7.5	.787 20.0																
	FSNBS5-4	FSNS5-4	#8	.169 4.3	.299 7.6	.244 6.2	.728 18.5								.236 6.0	.220 5.6	.134 3.4	.059 1.5	.039 1.0		1000		
	FSNB5-5	FSN5-5	#10	.209 5.3	.335 8.5	.295 7.5	.787 20.0																1000
	FSNBS5-5	FSNS5-5	#10	.209 5.3	.299 7.6	.244 6.2	.728 18.5																

UL cUL ALL LISTED
Ⓢ : NOT UL AND C-UL LISTED