


NON-INSULATED LOCKING SPADE TERMINALS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM		d2	W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm ²	LSNB1-3.2	LSN1-3.2	#4	.126 3.2	.252 6.4	.256 6.5	.630 16.0	.189 4.8	.134 3.4	.067 1.7	.030 0.75	IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:1.25	1000
	LSNB1-3.7	LSN1-3.7	#6	.146 3.7									1000
	LSNBS1-4	LSNS1-4	#8	.169 4.3									1000
	LSNBL1-4	LSNL1-4	#8	.169 4.3									1000
	LSNBS1-5	LSNS1-5	#10	.209 5.3									1000
	LSNBL1-5	LSNL1-5	#10	.209 5.3									1000
16-14 A.W.G. 1.5-2.5 mm ²	LSNB2-3.2	LSN2-3.2	#4	.126 3.2	.236 6.0	.256 6.5	.630 16.0	.189 4.8	.161 4.1	.091 2.3	.031 0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:2	1000
	LSNB2-3.7	LSN2-3.7	#6	.146 3.7									1000
	LSNBL2-3.7	LSNL2-3.7	#6	.146 3.7									1000
	LSNB2-4	LSN2-4	#8	.169 4.3									1000
	LSNBL2-4	LSNL2-4	#8	.169 4.3									1000
	LSNBS2-5	LSNS2-5	#10	.209 5.3									1000
	LSNBL2-5	LSNL2-5	#10	.209 5.3									1000
	LSNB2-6	LSN2-6	1/4	.252 6.4									1000
12-10 A.W.G. 4-6 mm ²	LSNBS5-3.7	LSNS5-3.7	#6	.146 3.7	.307 7.8	.276 7.0	.717 18.2	.236 6.0	.220 5.6	.134 3.4	.039 1.0	IZUMI MODEL 5N18 WITH DIE INDEX NO:5.5 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:5.5	1000
	LSNB5-3.7	LSN5-3.7	#6	.146 3.7									1000
	LSNB5-4	LSN5-4	#8	.169 4.3									1000
	LSNB5-5	LSN5-5	#10	.209 5.3									1000
	LSNB5-6	LSN5-6	1/4	.252 6.4									1000

ALL LISTED