


VINYL-INSULATED (MOLDED EASY ENTRY) LOCKING SPADE TERMINALS



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: VINYL

INSULATION COLOR:

22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■ 12-10 A.W.G.: YELLOW ■

TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} / _{mm}						CRIMPING TOOL	Q'TY BOX	
	BRAZED SEAM	BUTTED SEAM	d2	W	F	L	E	D	d1	T			
22-16 A.W.G. 0.5-1.5 mm ²	LSVYB1-3.2	LSVY1-3.2	#4	.126 3.2	.252 6.4	.256 6.5	.866 22.0	.433 11.0	.157 4.0	.067 1.7	.030 0.75	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
	LSVYB1-3.7	LSVY1-3.7	#6	.146 3.7									1000
	LSVYBS1-4	LSVYS1-4	#8	.169 4.3	.283 7.2								1000
	LSVYBL1-4	LSVYL1-4	#8	.169 4.3	.319 8.1								1000
	LSVYBS1-5	LSVYS1-5	#10	.209 5.3									1000
	LSVYBL1-5	LSVYL1-5	#10	.209 5.3	.374 9.5								1000
16-14 A.W.G. 1.5-2.5 mm ²	LSVYB2-3.2	LSVY2-3.2	#4	.126 3.2	.236 6.0	.256 6.5	.866 22.0	.433 11.0	.177 4.5	.091 2.3	.031 0.8	IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
	LSVYB2-3.7	LSVY2-3.7	#6	.146 3.7									1000
	LSVYBL2-3.7	LSVYL2-3.7	#6	.146 3.7	.283 7.2								1000
	LSVYB2-4	LSVY2-4	#8	.169 4.3									1000
	LSVYBL2-4	LSVYL2-4	#8	.169 4.3	.319 8.1								1000
	LSVYBS2-5	LSVYS2-5	#10	.209 5.3									1000
	LSVYBL2-5	LSVYL2-5	#10	.209 5.3	.366 9.3								1000
	LSVYB2-6	LSVY2-6	1/4	.252 6.4									1000
12-10 A.W.G. 4-6 mm ²	LSVYBS5-3.7	LSVYS5-3.7	#6	.146 3.7	.307 7.8	.276 7.0	.992 25.2	.512 13.0	.252 6.4	.134 3.4	.039 1.0	IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500
	LSVYB5-3.7	LSVY5-3.7	#6	.146 3.7									500
	LSVYB5-4	LSVY5-4	#8	.169 4.3	.327 8.3								500
	LSVYB5-5	LSVY5-5	#10	.209 5.3	.354 9.0								500
	LSVYB5-6	LSVY5-6	1/4	.252 6.4	.472 12.0								.472 12.0

UL cUL ALL LISTED