

NYLON-INSULATED DOUBLE CRIMP MALE DISCONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	3	4	7	10	15	20	24

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: NYLON TERMINAL MATERIAL: BRASS


INSULATION COLOR:

22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■ 12-10 A.W.G.: YELLOW ■

DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL

TERMINAL BARREL I.D.:

22-16 A.W.G.: C=1.7mm 16-14 A.W.G.: C=2.3mm 12-10 A.W.G.: C=3.4mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	NEMA TAB	DIMENSION ^{inch} mm						CRIMPING TOOL	Q'TY BOX	
			W	F	L	B	D	T			
22-16 A.W.G. 0.5-1.5 mm ²	MDNYD1-110(5)	.020×.110 (0.5×2.8)	.110 2.8	.256 6.5	.768 19.5	.433 11.0	.157 4.0	.020 0.5	IZUMI MODEL 34 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:RED	1000	
	MDNYD1-110(8)	.032×.110 (0.8×2.8)						.016 0.4		1000	
	MDNYD1-187(5)	.020×.187 (0.5×4.75)	.189 4.8	.787 20.0	.020 0.5			1000			
	MDNYD1-187(8)	.032×.187 (0.8×4.75)						.016 0.4		1000	
	MDNYD1-250	.032×.250 (0.8×6.35)	.250 6.35	.303 7.7	.866 22.0					1000	
16-14 A.W.G. 1.5-2.5 mm ²	MDNYD2-110(5)	.020×.110 (0.5×2.8)	.110 2.8	.256 6.5	.768 19.5	.433 11.0	.197 5.0	.020 0.5	IZUMI MODEL 34 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:BLUE	1000	
	MDNYD2-110(8)	.032×.110 (0.8×2.8)		.264 6.7						1000	
	MDNYD2-187(5)	.020×.187 (0.5×4.75)	.189 4.8	.256 6.5	.787 20.0			.016 0.4		1000	
	MDNYD2-187(8)	.032×.187 (0.8×4.75)								.264 6.7	1000
	MDNYD2-250	.032×.250 (0.8×6.35)	.250 6.35	.303 7.7	.874 22.2					1000	
12-10 A.W.G. 4-6 mm ²	MDNYD5-250	.032×.250 (0.8×6.35)	.250 6.35	.303 7.7	.945 24.0	.512 13.0	.256 6.5	.016 0.4	IZUMI MODEL 5 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:YELLOW	500	