

VINYL-INSULATED (MOLDED EASY ENTRY) MULTIPLE-STUD RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50


MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: VINYL

INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d3-d2		W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm ²	MSRVYB1-2237	MSRVY1-2237	#2 #4 #6	.087 2.2 .126 3.2 .146 3.7	.280 7.1	.280 7.1	.909 23.1					IZUMI MODEL 34 WITH DIE INDEX COLOR: RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR: RED	1000
	MSRVYB1-3753	MSRVY1-3753	#6 #8 #10	.146 3.7 .169 4.3 .209 5.3	.339 8.6	.311 7.9	.996 25.3	.433 11.0	.157 4.0	.067 1.7	.030 0.75		1000
16-14 A.W.G. 1.5-2.5 mm ²	MSRVYB2-2237	MSRVY2-2237	#2 #4 #6	.087 2.2 .126 3.2 .146 3.7	.280 7.1	.280 7.1	.909 23.1					IZUMI MODEL 34 WITH DIE INDEX COLOR: BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR: BLUE	1000
	MSRVYB2-3753	MSRVY2-3753	#6 #8 #10	.146 3.7 .169 4.3 .209 5.3	.339 8.6	.311 7.9	.996 25.3	.433 11.0	.177 4.5	.091 2.3	.031 0.8		1000
12-10 A.W.G. 4-6 mm ²	MSRVYB5-3753	MSRVY5-3753	#6 #8 #10	.146 3.7 .169 4.3 .209 5.3	.390 9.9	.350 8.9	1.154 29.3	.512 13.0	.252 6.4	.134 3.4	.039 1.0	IZUMI MODEL 5 WITH DIE INDEX COLOR: YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR: YELLOW	1000

UL cUL ALL LISTED