

HEAT SHRINKABLE-BULLET DISCONNECTORS "HD"(DOUBLE CRIMP TYPE)

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	3	4	7	10	15	20	24


MAXIMUM ELECTRICAL RATING: 300 VOLTS MAX.

SHRINK TEMP.: 150°C OPERATING TEMP.: -40°C~+105°C

INSULATION MATERIAL: HIGH DENSITY PE.

INSULATION MATERIAL: WITH COPPER SLEEVE ON BARREL

TERMINAL MATERIAL: BRASS



WIRE RANGE A.W.G. mm ²	ITEM NO.	W		D		L		INSULATED COLOR	CRIMPING TOOL	QTY BOX
		inch	mm	inch	mm	inch	mm			
22-16 A.W.G. 0.5-1.5 mm ²	MPHD1-156	.157	4.0	.217	5.5	1.299	33.0	RED	K.S. MODEL KST2000A WITH DIE INDEX COLOR:RED	500
16-14 A.W.G. 1.5-2.5 mm ²	MPHD2-156	.157	4.0	.236	6.0	1.299	33.0	BLUE	K.S. MODEL KST2000A WITH DIE INDEX COLOR:BLUE	500
	MPHD2-180	.177	4.5							500
	MPHD2-195	.197	5.0							500
12-10 A.W.G. 4-6 mm ²	MPHD5-195	.197	5.0	.319	8.1	1.398	35.5	YELLOW	K.S. MODEL KST2000A WITH DIE INDEX COLOR:YELLOW	500