


NON-INSULATED MULTIPLE-STUD RING TERMINALS



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14
AMP.	9	12	17	18	30

TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} mm						CRIMPING TOOL	Q'TY BOX						
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1			T					
22-16 A.W.G. 0.5-1.5 mm ²	MSRNB1-2237	MSRN1-2237	#2	.087 2.2									IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25 OR K.S. MODEL KST2000D-1322 LY-2045A LY-2045C LY-2045D WITH DIE INDEX NO:125	1000				
			#4	.126 3.2											.280 7.1	.280 7.1	.681 17.3	
				#6	.146 3.7									IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO.:22-18 OR K.S. MODEL KM-70L WITH DIE SET NO:DIE-1322 WITH DIE INDEX NO.:22-18	1000			
				#8	.169 4.3											.339 8.6	.311 7.9	.768 19.5
16-14 A.W.G. 1.5-2.5 mm ²	MSRNB2-2237	MSRN2-2237	#2	.087 2.2									IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 LY-2045A LY-2045C LY-2045D WITH DIE INDEX NO:2	1000				
			#4	.126 3.2											.280 7.1	.280 7.1	.681 17.3	
				#6	.146 3.7									IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO.:16-14 OR K.S. MODEL KM-70L WITH DIE SET NO:DIE-1322 WITH DIE INDEX NO.:16-14	1000			
				#8	.169 4.3											.339 8.6	.311 7.9	.768 19.5
	MSRNB2-3753	MSRN2-3753	#10	.209 5.3														