

HEAT SHRINKABLE-RING TERMINALS "HB"(BRAZED TYPE)

MAXIMUM ELECTRIC CURRENT:


A.W.G.	22	20	18	16
AMP.	9	12	17	18

MAXIMUM ELECTRICAL RATING: 600 VOLTS MAX.

SHRINK TEMP.: 150°C OPERATING TEMP.: -40°C~+105°C

INSULATION MATERIAL: HIGH DENSITY PE.

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION						INSULATED COLOR	CRIMPING TOOL	Q'TY BOX
		d2		W		L				
		inch	mm	inch	mm	inch	mm			
22-16 A.W.G. <										

 ALL LISTED