

HEAT SHRINKABLE-RING TERMINALS "HD"(DOUBLE CRIMP TYPE)

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16
AMP.	9	12	17	18


MAXIMUM ELECTRICAL RATING: 600 VOLTS MAX.

SHRINK TEMP.: 150°C OPERATING TEMP.: -40°C~+105°C

INSULATION MATERIAL: HIGH DENSITY PE.

INSULATION MATERIAL: WITH COPPER SLEEVE ON BARREL

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION						INSULATED COLOR	CRIMPING TOOL	Q'TY BOX	
		d2		W		L					
		inch	mm	inch	mm	inch	mm				
22-16 A.W.G.	RHD1-2.5	#2	2.4	.217	5.5	1.161	29.5	RED	K.S. MODEL KST2000G WITH DIE INDEX COLOR:RED	1000	
	RHD1-3.2	#4	3.2							1000	
	RHDS1-3.7	#6	3.7							1.201	30.5
	RHDM1-3.7	#6	3.7	.260	6.6	1.236	31.4			1000	
	RHDL1-3.7	#6	3.7	.315	8.0	1.291	32.8			1000	
	RHDS1-4	#8	4.3	.260	6.6	1.236	31.4			1000	
	RHDL1-4	#8	4.3	.315	8.0	1.291	32.8			1000	
	RHD1-5	#10	5.3							1000	
	0.5-1.5 mm ²	RHDL1-5	#10	5.3	.457	11.6	1.555			39.5	1000
		RHD1-6	1/4	6.4			1.496			38.0	500
RHD1-7		5/16	7.4	1.535			39.0	500			
RHD1-8		5/16	8.4	1.496			38.0	500			
RHD1-10		3/8	10.5	.535	13.6	1.638	41.6	500			
RHDL1-10		3/8	10.5	.756	19.2	1.874	47.6	500			
RHD1-12		1/2	13.0			1.866	47.4	500			
RHD1-13		9/16	14.0			1.874	47.6	500			
RHD1-14	9/16	15.0	1.063	27.0	2.217	56.3	500				
RHD1-16	5/8	17.0					500				
RHD1-20	3/4	21.0					500				

UL US ALL LISTED