

# HEAT SHRINKABLE-RING TERMINALS "HD"(DOUBLE CRIMP TYPE)

**MAXIMUM ELECTRIC CURRENT:**

|        |    |    |
|--------|----|----|
| A.W.G. | 12 | 10 |
| AMP.   | 35 | 50 |


**MAXIMUM ELECTRICAL RATING: 600 VOLTS MAX.**

**SHRINK TEMP.: 150°C OPERATING TEMP.: -40°C~+105°C**

**INSULATION MATERIAL: HIGH DENSITY PE.**

**INSULATION MATERIAL: WITH COPPER SLEEVE ON BARREL**

**TERMINAL MATERIAL: COPPER**



| WIRE<br>RANGE<br>A.W.G.<br>mm <sup>2</sup>                                             | ITEM NO.  | DIMENSION |      |       |      |       |      | INSULATED<br>COLOR | CRIMPING<br>TOOL                                         | Q'TY<br>BOX |
|----------------------------------------------------------------------------------------|-----------|-----------|------|-------|------|-------|------|--------------------|----------------------------------------------------------|-------------|
|                                                                                        |           | d2        |      | W     |      | L     |      |                    |                                                          |             |
|                                                                                        |           | inch      | mm   | inch  | mm   | inch  | mm   |                    |                                                          |             |
| 12-10<br>A.W.G.<br><br><br><br><br><br><br><br><br><br><br><br><br>4-6 mm <sup>2</sup> | RHD5-3.2  | #4        | 3.2  | .283  | 7.2  | 1.327 | 33.7 | YELLOW             | K.S. MODEL<br>KST2000G<br>WITH DIE INDEX<br>COLOR:YELLOW | 500         |
|                                                                                        | RHD5-3.7  | #6        | 3.7  |       |      | 1.339 | 34.0 |                    |                                                          | 500         |
|                                                                                        | RHDL5-3.7 | #6        | 3.7  | .374  | 9.5  | 1.465 | 37.2 |                    |                                                          | 500         |
|                                                                                        | RHDS5-4   | #8        | 4.3  | .283  | 7.2  | 1.335 | 33.9 |                    |                                                          | 500         |
|                                                                                        | RHDL5-4   | #8        | 4.3  | .374  | 9.5  | 1.449 | 36.8 |                    |                                                          | 500         |
|                                                                                        | RHD5-4.7  | #8        | 4.7  |       |      | 1.488 | 37.8 |                    |                                                          | 500         |
|                                                                                        | RHD5-5    | #10       | 5.3  |       |      | 1.449 | 36.8 |                    |                                                          | 500         |
|                                                                                        | RHDL5-5   | #10       | 5.3  | .488  | 12.4 | 1.673 | 42.5 |                    |                                                          | 500         |
|                                                                                        | RHD5-6    | 1/4       | 6.4  | .472  | 12.0 | 1.551 | 39.4 |                    |                                                          | 500         |
|                                                                                        | RHDM5-6   | 1/4       | 6.4  |       |      | 1.701 | 43.2 |                    |                                                          | 500         |
|                                                                                        | RHD5-7    | 5/16      | 7.4  |       |      | 1.594 | 40.5 |                    |                                                          | 500         |
|                                                                                        | RHD5-8    | 5/16      | 8.4  | .591  | 15.0 | 1.732 | 44.0 |                    |                                                          | 500         |
|                                                                                        | RHD5-10   | 3/8       | 10.5 |       |      |       |      |                    |                                                          | 500         |
|                                                                                        | RHD5-12   | 1/2       | 13.0 | .756  | 19.2 | 1.937 | 49.2 |                    |                                                          | 500         |
|                                                                                        | RHD5-13   | 9/16      | 14.0 |       |      | 1.961 | 49.8 |                    |                                                          | 500         |
|                                                                                        | RHD5-14   | 9/16      | 15.0 | 1.260 | 32.0 |       |      |                    |                                                          | 500         |
|                                                                                        | RHD5-16   | 5/8       | 17.0 |       |      |       |      |                    |                                                          | 500         |
|                                                                                        | RHD5-18   | 11/16     | 19.0 |       |      |       |      |                    |                                                          | 500         |
|                                                                                        | RHD5-20   | 3/4       | 21.0 |       |      |       |      |                    |                                                          | 500         |

cUL<sub>us</sub> ALL LISTED