



## Sample Kit Contents

| KEMET<br>Part Number | Capacitance<br>Value (μF) | Dimensions in mm |      |      | Lead<br>Spacing (p) | Resistance<br>(Ω) | Quantity |
|----------------------|---------------------------|------------------|------|------|---------------------|-------------------|----------|
|                      |                           | B                | H    | L    |                     |                   |          |
| P410QM223M300AH101   | 22                        | 7.3              | 13.0 | 18.5 | 15.2                | 100               | 10       |
| P410QS333M300AH101   | 33                        | 8.5              | 14.3 | 18.5 | 15.2                | 100               | 10       |
| P410CJ473M300AH101   | 47                        | 9.0              | 15.0 | 24.0 | 20.3                | 100               | 10       |
| P410CP683M300AH101   | 68                        | 11.3             | 16.5 | 24.0 | 20.3                | 100               | 10       |
| P410EE104M300AH101   | 0.1                       | 10.6             | 16.1 | 30.5 | 25.4                | 100               | 10       |

## Dimensions – Millimeters


[www.kemet.com/P410](http://www.kemet.com/P410)

| Size Code | p       |           | B       |           | H       |           | L       |           | d       |           |
|-----------|---------|-----------|---------|-----------|---------|-----------|---------|-----------|---------|-----------|
|           | Nominal | Tolerance | Nominal | Tolerance | Nominal | Tolerance | Nominal | Tolerance | Nominal | Tolerance |
| QM        | 15.2    | +/-0.4    | 7.3     | Maximum   | 13.0    | Maximum   | 18.5    | Maximum   | 0.8     | +/-0.05   |
| QS        | 15.2    | +/-0.4    | 8.5     | Maximum   | 14.3    | Maximum   | 18.5    | Maximum   | 0.8     | +/-0.05   |
| CJ        | 20.3    | +/-0.4    | 9.0     | Maximum   | 15.0    | Maximum   | 24.0    | Maximum   | 0.8     | +/-0.05   |
| CP        | 20.3    | +/-0.4    | 11.3    | Maximum   | 16.5    | Maximum   | 24.0    | Maximum   | 0.8     | +/-0.05   |
| EE        | 25.4    | +/-0.4    | 10.6    | Maximum   | 16.1    | Maximum   | 30.5    | Maximum   | 1.0     | +/-0.05   |

**Note: See Ordering Options Table for lead length (LL) options.**