

## PULSED LASER DIODE LTE-L201E-01

### Descriptions

The LTE-L201E-01 is a nano-stacked pulsed laser diode in a TO56 package.

### Applications

- Electronic equipment
- Equipment illumination
- Laser range finder, speed measurement
- Long range 3D sensing
- IR night illumination, motion detection, CCTV surveillance



### Features

- 75W peak power at 30A operating current
- 95W peak power at 40A operating current
- Laser wavelength 905nm
- Suited for short laser pulses from 1ns to 100ns
- Laser aperture 200um x 10um

### Ordering Information

Part Number	Packaging Type	Package	Quantity
LTE-L201E-01	Plastic Tray	TO56	Contact Sales

## PULSED LASER DIODE LTE-L201E-01

### Outline Dimensions




Figure 1 Dimensional drawings

### Maximum Ratings

Operating  $T_{OP} = 25^{\circ}\text{C}$ , unless otherwise stated.

Parameter	Symbol	Min.	Max.	Unit
Operating Temperature	$T_{OP}$	-40	85	$^{\circ}\text{C}$
Storage Temperature	$T_{ST}$	-40	100	$^{\circ}\text{C}$
Peak Output Power	$P_{PEAK}$		110	W
Operating Current	$I_{OP}$		40	A
Pulse Width	$T_P$		100	ns
Duty Cycle	$D_C$		0.1	%
Reverse Voltage	$V_R$		5	V
Soldering Temperature – Note 1				
- 10 seconds max			260	$^{\circ}\text{C}$
- 2mm from bottom edge of case				

Notes:

- Based on IEC60068-2-20 (edition 6.0), Resistance to soldering heat, Test Tb, Method 1 solder bath, Pb-free; Depth of immersion 2mm from bottom edge of the case, with PCB as spacer.

# PULSED LASER DIODE LTE-L201E-01

## Electrical-Optical Specifications

Conditions, unless otherwise stated:

Operating Current  $I_{OP}$  = 40A; Pulse Width = 100ns; Duty Cycle = 0.01%; Operating  $T_{OP}$  = 25°C.

Description	Symbol	Min.	Typ.	Max.	Unit
Peak Output Power @ 30A $I_{OP}$	$P_{PEAK}$		75		W
Peak Output Power @ 40A $I_{OP}$	$P_{PEAK}$	80	95		W
Operating Current	$I_{OP}$		30	40	A
Threshold Current	$I_{TH}$		0.5		A
Operating Voltage	$V_{OP}$		13	15	V
Peak Wavelength	$\lambda_{PEAK}$	895	905	915	nm
Spectral Width (FWHM)	$\Delta\lambda$		9		nm
Peak Wavelength Temperature Coefficient			0.25		nm/K
Beam Divergence Parallel to pn-Junction	$\theta_{  }$		10		Deg
Beam Divergence Perpendicular to pn-Junction	$\theta_{\perp}$		25		Deg
Emitter Aperture Size	w x h		200x10		$\mu m^2$
Thermal Resistance – Junction to Solder Point – Note2	$R_{JS}$		38		K/W

Notes:

2. Mounted on 16mm<sup>2</sup> pad PCB


## PULSED LASER DIODE LTE-L201E-01

### Characteristics


Conditions, unless otherwise stated: Operating Current  $I_{OP} = 40A$ ; Pulse Width = 100ns; Duty Cycle = 0.01%;

Operating  $T_{OP} = 25^{\circ}C$ .

**Figure 2 Spectral Distribution Plot**



**Figure 3 Forward Voltage vs Drive Current**



## PULSED LASER DIODE LTE-L201E-01

Figure 4: Far Field Pattern Perpendicular to PN-Junction





Figure 5: Far Field Pattern Parallel to PN-Junction



## PULSED LASER DIODE LTE-L201E-01

Figure 6 Peak Power vs Drive Current





Figure 7 Peak Power vs Ambient Temperature



## PULSED LASER DIODE LTE-L201E-01

Figure 8 Peak Wavelength vs Drive Current





Figure 9 Peak Wavelength vs Ambient Temperature



**PULSED LASER DIODE  
LTE-L201E-01****Laser Safety**

Depending on the mode of operation, the device produces invisible electromagnetic radiation that may be harmful to the human eye. It is the responsibility of the user incorporating a laser into a product to certify the class of use and ensure that it follows the safety precautions given in IEC 60825-1.



## PULSED LASER DIODE LTE-L201E-01

### Revision Table

Version	Update	Page	Date
1.0	Datasheet created	Total 9 pages	18/04/2023