



OCV Series

Features

- 105°C, 2,000 hours assured
- Ultra low ESR, solid capacitors of SMD type
- RoHS compliance




Marking color: Blue

Specifications

Items	Performance																							
Category Temperature Range	-55℃ ~ +105℃																							
Capacitance Tolerance	±20% (at 120 Hz, 20℃)																							
Leakage Current (at 20℃)*	Rated voltage applied, after 2 minutes at 20℃. See Standard Ratings																							
Tanδ (at 120 Hz, 20℃)	See Standard Ratings																							
ESR (at 100k ~ 300k Hz, 20℃)	See Standard Ratings																							
Endurance	<table><tr><td>Test Time</td><td colspan="3">2,000 Hrs</td></tr><tr><td>Capacitance Change</td><td colspan="3">Within ±20% of initial value</td></tr><tr><td>Tanδ</td><td colspan="3">Less than 150% of specified value</td></tr><tr><td>ESR</td><td colspan="3">Less than 150% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="3">Within specified value</td></tr></table>				Test Time	2,000 Hrs			Capacitance Change	Within ±20% of initial value			Tanδ	Less than 150% of specified value			ESR	Less than 150% of specified value			Leakage Current	Within specified value		
	Test Time	2,000 Hrs																						
	Capacitance Change	Within ±20% of initial value																						
	Tanδ	Less than 150% of specified value																						
	ESR	Less than 150% of specified value																						
Leakage Current	Within specified value																							
	* The above specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage applied for 2,000 hours at 105℃.																							
Moisture Resistance	<table><tr><td>Test Time</td><td colspan="3">1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td colspan="3">Within ±20% of initial value</td></tr><tr><td>Tanδ</td><td colspan="3">Less than 150% of specified value</td></tr><tr><td>ESR</td><td colspan="3">Less than 150% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="3">Within specified value</td></tr></table>				Test Time	1,000 Hrs			Capacitance Change	Within ±20% of initial value			Tanδ	Less than 150% of specified value			ESR	Less than 150% of specified value			Leakage Current	Within specified value		
	Test Time	1,000 Hrs																						
	Capacitance Change	Within ±20% of initial value																						
	Tanδ	Less than 150% of specified value																						
	ESR	Less than 150% of specified value																						
Leakage Current	Within specified value																							
	* The above specifications shall be satisfied when the capacitors are restored to 20℃ after subjecting them at 60℃, 90 ~ 95% RH for 1,000 hours. Leakage current should be tested after voltage treatment*.																							
Resistance to Soldering Heat * (Please refer to page 26 for reflowsoldering conditions)	<table><tr><td>Capacitance Change</td><td colspan="3">Within ±10% of initial value</td></tr><tr><td>Tanδ</td><td colspan="3">Within specified value</td></tr><tr><td>ESR</td><td colspan="3">Within specified value</td></tr><tr><td>Leakage Current</td><td colspan="3">Within specified value</td></tr></table>				Capacitance Change	Within ±10% of initial value			Tanδ	Within specified value			ESR	Within specified value			Leakage Current	Within specified value						
	Capacitance Change	Within ±10% of initial value																						
	Tanδ	Within specified value																						
	ESR	Within specified value																						
Leakage Current	Within specified value																							
Ripple Current and Frequency Multipliers	<table><tr><td>Frequency (Hz)</td><td>120 ≤ f < 1k</td><td>1k ≤ f < 10k</td><td>10k ≤ f < 100k</td><td>100k ≤ f < 500k</td></tr><tr><td>Multiplier</td><td>0.05</td><td>0.3</td><td>0.7</td><td>1.0</td></tr></table>				Frequency (Hz)	120 ≤ f < 1k	1k ≤ f < 10k	10k ≤ f < 100k	100k ≤ f < 500k	Multiplier	0.05	0.3	0.7	1.0										
Frequency (Hz)	120 ≤ f < 1k	1k ≤ f < 10k	10k ≤ f < 100k	100k ≤ f < 500k																				
Multiplier	0.05	0.3	0.7	1.0																				

* For any doubt about measured values, measure the leakage current again after the following voltage treatment.
Voltage treatment: DC rated voltage is applied to the capacitors for 2 hours at 105 °C.

Diagram of Dimensions



Lead Spacing and Diameter



Unit: mm

φ D	L	A	B	C	W	P ± 0.2
5	5.7 ± 0.3	5.3	5.3	5.9	0.5 ~ 0.8	1.5
6.3	5.9 +0.1/-0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0
6.3	7.0 ± 0.2	6.6	6.6	7.2	0.5 ~ 0.8	2.0
8	6.7 ± 0.3	8.3	8.3	9.0	0.7 ~ 1.1	3.1
8	12.0 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1
10	7.7 ± 0.3	10.3	10.3	11.0	0.7 ~ 1.3	4.7
10	9.9 +0.1/-0.3	10.3	10.3	11.0	0.7 ~ 1.3	4.7
10	12.6 +0.1/-0.4	10.3	10.3	11.0	0.7 ~ 1.3	4.7

Marking

φ D = 5 ~ 6.3

φ D = 8 ~ 10





Dimension: ϕ D×L(mm)

Ripple Current: mA/rms at 100k Hz, 105°C

Standard Ratings

Rated Volt. (V)	Surge Voltage (V)	Capacitance (μ F)	Size ϕ D×L(mm)	Tan δ (120 Hz, 20°C)	L C (μ A)	E S R (m Ω /at 100k ~ 300k Hz, 20°C max.)	Rated R. C. (mA/rms at 100k Hz, 105°C)
2.5V (0E)	2.9	220	6.3 × 5.9	0.12	110	25	2,500
		560	8 × 6.7	0.12	280	23	3,100
		680	8 × 12	0.18	340	12	4,770
		1,000	10 × 7.7	0.12	500	19	4,240
		1,200	10 × 9.9	0.18	750	13	5,200
		1,500	10 × 12.6	0.18	750	10	5,500
4V (0G)	4.6	150	5 × 5.7	0.12	120	30	1,490
			6.3 × 5.9		120	26	2,450
		220	8 × 6.7		176	25	3,020
		330	8 × 6.7		264	25	3,020
		470	10 × 7.7		376	20	4,130
		560	8 × 12	0.18	448	12	4,770
		680	10 × 7.7	0.12	544	20	4,130
		820	10 × 9.9	0.18	656	13	5,200
		1,200	10 × 12.6	0.18	960	10	5,500
6.3V (0J)	7.2	82	6.3 × 5.9	0.12	103	27	2,400
			5 × 5.7		126	35	1,380
			6.3 × 5.9		126	27	2,400
		120	6.3 × 7		151	30	2,010
			6.3 × 7		189	30	2,250
		150	8 × 6.7		189	25	3,020
			6.3 × 7		277	30	2,250
		220	8 × 6.7		277	25	3,020
			10 × 7.7	0.15	416	20	4,130
		330	8 × 12		592	12	4,770
		560	10 × 9.9		706	16	4,700
		820	10 × 12.6		1,033	10	5,500
10V (1A)	12.0	47	5 × 5.7	0.12	94	40	1,270
		56	6.3 × 5.9	0.10	112	31	2,250
		150	8 × 6.7	0.10	300	27	2,800
		330	8 × 12	0.15	660	14	4,420
			10 × 7.7	0.10	660	24	3,770
		470	10 × 9.9	0.15	940	18	4,400
		560	10 × 12.6	0.15	1,120	12	5,300
16V (1C)	18.0	22	5 × 5.7	0.12	70	45	1,210
		47	6.3 × 5.9	0.10	150	50	1,650
		82	8 × 6.7	0.10	262	30	2,700
		180	8 × 12	0.15	576	16	4,360
			10 × 7.7	0.10	576	26	3,430
		220	10 × 9.9	0.15	704	20	4,200
		330	10 × 12.6	0.15	792	14	5,050
		820	10 × 12.6	0.12	2,624	18	4,200



Dimension: ϕ D×L(mm)

Ripple Current: mA/rms at 100k Hz, 105°C

Standard Ratings

Rated Volt. (V)	Surge Voltage (V)	Capacitance (μ F)	Size ϕ D×L(mm)	Tan δ (120 Hz, 20°C)	L C (μ A)	E S R (m Ω /at 100k ~ 300k Hz, 20°C max.)	Rated R. C. (mA/rms at 100k Hz, 105°C)
20V (1D)	23.0	22	6.3 × 5.9	0.10	88	50	1,650
		47	8 × 6.7		188	45	2,000
		82	10 × 7.7		328	40	2,500
		100	8 × 12	0.15	400	24	3,320
			10 × 9.9		400	25	3,700
		150	10 × 12.6		600	20	4,320
		330	10 × 12.6	0.12	1,320	26	2,700
25V (1E)	29.0	6.8	6.3 × 5.9	0.10	170	80	1,200
		10	8 × 6.7		125	60	1,500
		22	10 × 7.7		275	50	2,000
		33	8 × 12	0.12	413	30	2,980
		56	10 × 12.6		700	28	3,800
		270	10 × 12.6		1,350	27	2,700
35V (1V)	40.0	39	8 × 12	0.12	273	31	2,100
		68	10 × 12.6	0.12	476	28	2,700

Part Numbering System

OCV Series	470 μ F	±20%	6.3V	Carrier Tape		8 ϕ × 12L	Pb-free and Coated Case
OCV	471	M	0J	TR	-	0812	
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size	Lead Wire and Case Type

Note: For more details, please refer to "Part Numbering System (SMD Type)" on page 15.