



RUK Series

Features

- 125°C, 3,000 ~ 5,000 hours assured
- For automobile modules and other high temperature applications
- RoHS Compliance




Sleeve & Marking Color: Black & White

Specifications

Items	Performance																														
Category Temperature Range	-40°C ~ +125°C																														
Capacitance Tolerance	± 20% (at 120Hz, 20°C)																														
Leakage Current (at 20°C)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF V = rated DC working voltage in V																														
Tanδ (at 120 Hz, 20°C)	<table><tr><td>Rated Voltage</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td>Tanδ (max)</td><td>0.15</td><td>0.12</td><td>0.10</td><td>0.10</td><td>0.08</td><td>0.08</td></tr></table>							Rated Voltage	10	16	25	35	50	63	Tanδ (max)	0.15	0.12	0.10	0.10	0.08	0.08										
Rated Voltage	10	16	25	35	50	63																									
Tanδ (max)	0.15	0.12	0.10	0.10	0.08	0.08																									
Low Temperature Characteristics (at 120Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td>Impedance</td><td>Z(-25°C) / Z(+20°C)</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Ratio</td><td>Z(-40°C) / Z(+20°C)</td><td>6</td><td>4</td><td>4</td><td>4</td><td>4</td><td>4</td></tr></table>							Rated Voltage		10	16	25	35	50	63	Impedance	Z(-25°C) / Z(+20°C)	3	2	2	2	2	2	Ratio	Z(-40°C) / Z(+20°C)	6	4	4	4	4	4
Rated Voltage		10	16	25	35	50	63																								
Impedance	Z(-25°C) / Z(+20°C)	3	2	2	2	2	2																								
Ratio	Z(-40°C) / Z(+20°C)	6	4	4	4	4	4																								
Endurance	<table><tr><td>Test Time</td><td>3,000 Hrs for φD ≤ 8mm; 5,000 Hrs for φD ≥ 10mm</td></tr><tr><td>Capacitance Change</td><td>With in ±20% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above Specifications shall be satisfied when the capacitors are restored to 20°C after applied with rated subjected to DC voltage with the rated ripple current is applied for 3,000 / 5,000 hours at 125°C.							Test Time	3,000 Hrs for φD ≤ 8mm; 5,000 Hrs for φD ≥ 10mm	Capacitance Change	With in ±20% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																
Test Time	3,000 Hrs for φD ≤ 8mm; 5,000 Hrs for φD ≥ 10mm																														
Capacitance Change	With in ±20% of initial value																														
Tanδ	Less than 200% of specified value																														
Leakage Current	Within specified value																														
Shelf Life Test	<table><tr><td>Test Time</td><td>1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>With in ±20% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td>Less than 500% of specified value</td></tr></table> * The above Specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 125°C without voltage applied.							Test Time	1,000 Hrs	Capacitance Change	With in ±20% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Less than 500% of specified value																
Test Time	1,000 Hrs																														
Capacitance Change	With in ±20% of initial value																														
Tanδ	Less than 200% of specified value																														
Leakage Current	Less than 500% of specified value																														
Ripple Current & Frequency Multipliers	<table><tr><th>Cap.(μF) \ Freq.(Hz)</th><th>120</th><th>1k</th><th>10k</th><th>100k up</th></tr><tr><td>0.47 ~ 100</td><td>1.00</td><td>1.70</td><td>1.88</td><td>2.00</td></tr><tr><td>150 ~ 470</td><td>1.00</td><td>1.45</td><td>1.58</td><td>1.65</td></tr><tr><td>1,000</td><td>1.00</td><td>1.20</td><td>1.25</td><td>1.33</td></tr></table>							Cap.(μF) \ Freq.(Hz)	120	1k	10k	100k up	0.47 ~ 100	1.00	1.70	1.88	2.00	150 ~ 470	1.00	1.45	1.58	1.65	1,000	1.00	1.20	1.25	1.33				
Cap.(μF) \ Freq.(Hz)	120	1k	10k	100k up																											
0.47 ~ 100	1.00	1.70	1.88	2.00																											
150 ~ 470	1.00	1.45	1.58	1.65																											
1,000	1.00	1.20	1.25	1.33																											

Diagram of Dimensions




Lead Spacing and Diameter

ϕD	8	10	12.5	16
P	3.5	5.0	5.0	7.5
ϕd	0.6			0.8
α	2.0			
β	0.5			

Unit: mm

The case size of 16×20 is suitable for below diagram:





Dimension: $\phi D \times L(\text{mm})$

Ripple Current: mA/rms at 120 Hz, 125°C

Dimension & Permissible Ripple Current

V. DC		10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)	
μF	Contents	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
10	100									8×11.5	56	8×11.5	56
22	220							8×11.5	75	10×12.5	99	10×12.5	99
33	330					8×11.5	92	10×12.5	108	10×16	133	10×16	133
47	470			8×11.5	100	10×12.5	129	10×16	142	10×16	159	10×20	173
100	101	10×12.5	154	10×16	190	10×16	208	10×20	225				
220	221	10×16	252	10×20	305	12.5×20	371	12.5×25	403	12.5×20	279	12.5×20	279
330	331	10×16	308	12.5×20	414	12.5×25	493	16×20	503				
470	471	10×20	399	12.5×25	537	16×20	601			16×20	459		
1,000	102	16×20	715										

Part Numbering System

RUK series	470 μF	$\pm 20\%$	16V	Bulk Package	Gas Type	12.5 $\phi \times 25\text{L}$	Pb-free and PET coating case
RUK	471	M	1C	BK	-	1325	
Series	Capacitance	Capacitance Tolerance	Rated Voltage	Lead Configuration & Package	Rubber Type	Case Size	Lead Wire and Coating Type

Note: For more details, please refer to "Part Numbering System (Radial Type)" on page 10.