PRODUCT NUMBER: 811-22-003-30-040101





(c)2023 Mill-Max Mfg Corp. | 516-922-6000
190 Pine Hollow Road, Oyster Bay, NY 11771

811-22-003-30-040101- SPECIFICATIONS

General Info	
Description[1]:	PCB Mount Spring-Loaded Header Vertical Surface Mount
Type:	Spring-Loaded
Category:	SLC Pin Header Strip
Mounting Style:	Surface Mount
# Pins:	3
Pitch:	.100" (2,540mm)
Rows:	Single Row
Product Lifecycle:	Active

Environmental Specs	
Temperature Range[2]:	-55/+125° C
Shock[3]:	No Elect. Discontinuity > 1µs @ 50g
Vibration[3]:	No Elect. Discontinuity > 1µs @ 10-2000HZ, 15 G
RoHS[4]:	Yes

Mechanical Specs	
Durability:	100,000 to 1,000,000 Cycles @ Mid-Stroke
SMT Pad Size:	.082" (2,083mm)

Materials	
Loose Pin/Receptacle #(Material):	2900 (Brass Alloy)
Shell Plating:	20µ" Gold over Nickel
Inner Plating:	(Spring) 10µ" Gold
Insulator Material:	Nylon 4/6

Technical Specs	
Initial Height:	.137" (3,480mm)
Stroke:	.039" (0,991mm)

Electrical Specs	
Rated Voltage:	100 VRMS/150 VDC
Insulation Resistance:	10,000 MΩ min.
Dielectric Withstanding Voltage:	1,000 VRMS min.

(c)2023 Mill-Max Mfg Corp. | 516-922-6000
190 Pine Hollow Road, Oyster Bay, NY 11771

NOTES:

1. **Standard Tolerances**
   Assembly tolerance: +/-.010" (.25mm)
   Connector Length “L”

Connector Length “L”	Tolerance
L ≤ 2” (L ≤ 50.8 mm)	+/- .005” (+/- .127 mm)
2< L ≤ 3” (50.8 < L ≤ 76.2 mm)	+ .007/ - .006” (+ .178/ -.152 mm)
3< L ≤ 4” (76.2 < L ≤ 101.6 mm)	+ .009 / - .007” (+ .229 / - .178 mm)
4< L ≤ 5” (101.6 < L ≤ 127 mm)	+ .011 / - .008” (+ .279 / - .203 mm)
5< L ≤ 6.4” (127 < L ≤ 162.56 mm)	+ .013 / - .009” (+ .330 / - .229 mm)

   Insulator width: +/-.005 (.13mm)
   Insulator height: +/-.005 (.13mm)
   Co-planarity of SMT connectors: .005" (.13mm) up to 1" (25.4mm) in connector length
   Insulator Flatness: .005" (.13mm) up to 1" (25.4mm) in connector length
   Pin Length: +/-.006 (.15mm)
   Pin Diameter: +/-.002 (.051mm)
   Pin Angle: +/-2°
2. Per IEC 60512-11-(4,-9,-10,-12)
3. For discrete pin only. Per IEC 60512-6-3: Test 6c: Shock
4. Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).

ADDITIONAL PARTS, PACKAGING, & ASSEMBLY INFO

Suggested P.C.B. Footprint



ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance , Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

RELATED LINKS AND DOCUMENTS

Engineering Notebook: (https://www.mill-max.com/engineering-notebooks/introduction-to-spring-loaded-pogo-pins-connectors)

Environmental Compliance: (https://www.mill-max.com/rohs)

(c)2023 Mill-Max Mfg Corp. | 516-922-6000