


NOTES: (T)

1. CHANGE OF MATERIAL IS NOT PERMITTED UNLESS APPROVED IN WRITING BY OTTO ENGINEERING PERSONNEL.
2. DRAWING TO BE INTERPRETED IN ACCORDANCE WITH THE CURRENT REVISION OF ASME Y14.5M.
3. TSI TO BE INTERPRETED AS THEORETICAL SHARP INTERSECTION.
4. THIS PART/PRODUCT IS TO BE MANUFACTURED WITH THE APPLICABLE REGULATIONS OF EC DIRECTIVES 2002/95/EC AND 2002/96/EC, RESTRICTION OF THE USE OF HAZARDOUS SUBSTANCES IN ELECTRICAL AND ELECTRONIC EQUIPMENT (RoHS) AND WASTE ELECTRICAL AND ELECTRONIC EQUIPMENT (WEEE).
5. PARTS SHALL BE FREE OF ALL CONTAMINANTS INCLUDING GREASE, DIRT, MACHINING OIL AND OTHER CONTAMINANTS.
6. PARTS SHALL BE PACKAGED IN A MANNER TO PREVENT SCRATCHING, BOWING OR OTHER DAMAGE DURING SHIPMENT.
7. PARTS SHALL BE FREE OF ALL CONTAMINANTS INCLUDING GREASE, DIRT, MACHINING OIL AND OTHER CONTAMINANTS.
8. BURRS NOT TO EXCEED .003" OTHERWISE STATED.

PART NO.	"A" DIM.	"B" DIM.
200302-2	.660	(.422)
200302-3	.695	(.429)
200302-4	.547	(.406)
200302-5	.230	(.355)

(U)



SCALE 1:1

200302

REV	OCN #	DATE	APR
K	005805	17 AUG 00	BDS
L	006944	20 DEC 00	RKK
M	009363	16 JUL 01	RKK
N	030936	23 FEB 06	KKK
P	031903	08 MAY 06	KKK
R	033140	27 JUL 06	KKK
T	049241	02 JUN 10	TAO
U	062101	12 JUL 11	TAO

MANUFACTURING		SPC		OTTO [®]		DESCRIPTION	
PROCESS: PASSIVATE PER AMS2700		MATERIAL: TYPE 301 STAINLESS STEEL FULL HARD .010 THK. PER AMS 5519 (MTL2489-XX)		CARPENTERSVILLE, ILLINOIS USA		A1, ACTUATOR (RIGHT HAND)	
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES. TOLERANCES ARE AS LISTED. MUST BE FREE FROM BURRS AND SHARP EDGES.		TOLERANCES .XX ± .01 .XXX ± .005 ANGLES ± 1° SURFACES 64 MICROINCH DO NOT SCALE DRAWING.		THIS DOCUMENT IS THE CONFIDENTIAL PROPERTY OF OTTO ENGINEERING, INC.. IT IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF OTTO ENGINEERING, INC..		DRWN. RW CHKD. TAO APPD. MCS WT.	SIZE B FSCM NO 21649 DRAWING NO. 200302 REV. U
						THIRD ANGLE PROJECTION	Scale 5:1 Sheet 1 OF 1