





© 2024 PennEngineering

ALL DIMENSIONS IN INCHES

DATE 18-MAR-2024

NOTE : DRAWING NOT TO SCALE

THREAD : .086-56 (#2-56)	MOUNTING HOLE DIA. : .188 +.003 -.000
MATERIAL: 300 Series Stainless Steel	PANEL THICKNESS: .130 MINIMUM
HEAT TREAT: NONE	MAX. PANEL HARDNESS: HRB 70 / HB 125 OR LESS
FINISH: Passivated and/or tested per ASTM A360	MIN CENTERLINE-TO-EDGE: 0.151
DESCRIPTION : PEM® CASTSERT™ Press-in Inserts - Unified	PennEngineering®
PART NO. : CKS-256-1	

EMAIL: TECHSUPPORT@PEMNET.COM
WWW.PEMNET.COM