

6

5

4

3

2


1

D

C

B

A




10.72±0.25 [1.422±.010]

5.92±0.13 [1.233±.005]

0.91±0.20 [1.036±.008]

5.59 [1.220] MAX.

7.19 [1.283]




2.84 [1.112] TYP.

D

C

B

A

2X
Ø 3.12±0.08 [1.123±.003]

CONTACT HOLE PATTERN

NOTES:

1. MATERIAL AND FINISHES:

INSULATOR: GLASS FILLED POLYESTER PER ASTM-D5927, UL 94V-0, COLOR: BLUE.

CONTACTS: PRECISION MACHINED COPPER ALLOY, 1.27µ [0.00050] GOLD OVER NICKEL PLATE.

SHELLS: STAINLESS STEEL, PASSIVATED.

ANGLE BRACKETS AND RIVETS : STAINLESS STEEL, PASSIVATED.

JACKSCREWS AND HEX NUTS: STAINLESS STEEL, PASSIVATED.

SPRING WASHERS: STAINLESS STEEL, PASSIVATED.

ALIGNMENT BAR: GLASS FILLED POLYESTER, UL 94V-0, COLOR: BLACK.

2. DETAILED PRODUCT, MECHANICAL AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST STANDARD DENSITY D-SUB PRODUCT PUBLICATION AT CONNECTPOSITRONIC.COM.

BY GJ	CHK SS	3RD ANGLE 	POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.	
APR AB	RELEASED DATE: 2024-04-12	SCALE NTS		
TOLERANCES ±0.03mm [.001 INCHES] FOR MALE CONTACT MATING DIAMETERS ±0.08mm [.003 INCHES] FOR CONTACT TERMINATION DIAMETERS ±0.13mm [.005 INCHES] FOR ALL OTHER DIAMETERS ±0.38mm [.015 INCHES] FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]				
PART NUMBER HDC15M5R60TS-15			SERIES HDC	
TITLE HDC15M5R60TS-15				
CREATED ON: 2024-04-12		SHEET SHEET 1 OF 1		REV A

6

5

4

3

2

1