

MATERIALS AND FINISHES:

MCX PLUG CONNECTOR:
MOLEX PN.73366-6020

BODY,CRIMP TUBE: BRASS
PLATED NICKEL

CENTER CONTACT: BRASS
PLATED GOLD

OUTER CONTACT: BERYLLIUM COPPER
PLATED GOLD

INSULATOR: PTFE



HEAT SHRINK TUBE,LABEL: PE, BLACK

CABLE: RG178B/U OR EQUIVALENT

TECHNICAL REQUIREMENTS

FREQUENCY RANGE: 0~3GHz
IMPEDANCE: 50 Ω
TEMPERATURE RANGE: -40~+85°C
WITHSTAND VOLTAGE(AC): 500V@0.5mA
CONTINUITY: 100% TEST

NOTE: PACKAGING BY PLASTIC BAG



73230-5973	48.000±.787	1219.20±20.00
73230-5972	24.000±.394	609.60±10.00
73230-5971	12.000±.394	304.80±10.00
73230-5970	6.000±.394	152.40±10.00
PART NO.	IN	MM
	L	

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
F_A = 0 F_E = 0 F_D = 0		DIMENSION UNITS	SCALE	CURRENT REV DESC: NEW RELEASED				molex									
		MM/INCH	4:1														
		GENERAL TOLERANCES (UNLESS SPECIFIED)															
ANGULAR TOL ± °		EC NO: 717300 DRWN: YHUANG11 2022/06/02 CHK'D: MYLU07 2022/08/11 APPR: LCHEN03 2022/08/11						CA, 50 OHMS, MCX PLUG TO MCX PLUG WITH RG178B/U CABLE, EWR#: 15229-A									
4 PLACES ±																	
3 PLACES ±																	
DIVISIONAL SYMBOLS						2 PLACES ±		PRODUCT CUSTOMER DRAWING									
						1 PLACE ±											
		0 PLACES ±															
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
						C-SIZE		73230		732305970		PSD		000		A	