




THIS DRAWING IS UNPUBLISHED.										RELEASED FOR PUBLICATION										- . - .									
© COPYRIGHT - By - ALL RIGHTS RESERVED.																													

LOC										DIST										REVISIONS									
AD										00										P LTR DESCRIPTION DATE DWN APVD									
																				- - SEE SHEET 1 - -									

7	4.400	.125	5.200	4.900	4.400	4.600	4.200	42	43/86	8-531020-3	OBSOLETE	8
7	3.700	.125	4.500	4.200	3.700	3.900	3.500	35	36/72	8-531020-2	OBSOLETE	8
7	6.600	0.160	7.400	7.100	6.600	6.800	6.400	64	65/160	8-531020-0	OBSOLETE	8
7	5.100	0.160	5.900	5.600	5.100	5.300	4.900	49	50/100	7-531020-9	OBSOLETE	8
7	4.400	0.160	5.200	4.900	4.400	4.600	4.200	42	43/86	7-531020-8	OBSOLETE	8
7	2.900	0.160	3.700	3.400	2.900	3.100	2.700	27	28/56	7-531020-7	OBSOLETE	8
7	3.200	0.160	4.000	3.700	3.200	3.400	3.000	30	31/62	7-531020-1	OBSOLETE	8
7	6.600	0.160	7.400	7.100	6.600	6.800	6.400	64	65/130	7-531020-0	OBSOLETE	8
7	6.100	0.160	6.900	6.600	6.100	6.300	5.900	59	60/120	6-531020-9	OBSOLETE	8
7	5.100	0.160	5.900	5.600	5.100	5.300	4.900	49	50/100	6-531020-8	OBSOLETE	8
7	4.400	0.160	5.200	4.900	4.400	4.600	4.200	42	43/86	6-531020-7	OBSOLETE	8
7	4.100	0.160	4.900	4.600	4.100	4.300	3.900	39	40/80	6-531020-5	OBSOLETE	8
7	3.700	0.160	4.500	4.200	3.700	3.900	3.500	35	36/72	6-531020-4	OBSOLETE	8
7	2.900	0.160	3.700	3.400	2.900	3.100	2.700	27	28/56	6-531020-3	OBSOLETE	8
7	2.600	0.160	3.400	3.100	2.600	2.800	2.400	24	25/50	6-531020-2	OBSOLETE	8
7	2.300	0.160	3.100	2.800	2.300	2.500	2.100	21	22/44	6-531020-1	OBSOLETE	8
7	6.600	.125	7.400	7.100	6.600	6.800	6.400	64	65/130	6-531020-0	OBSOLETE	8
7	5.100	.125	5.900	5.600	5.100	5.300	4.900	49	50/100	5-531020-8	OBSOLETE	8
7	4.100	.125	4.900	4.600	4.100	4.300	3.900	39	40/80	5-531020-5	OBSOLETE	8
7	2.600	.125	3.400	3.100	2.600	2.800	2.400	24	25/50	5-531020-2	OBSOLETE	8
7	2.300	.125	3.100	2.800	2.300	2.500	2.100	21	22/44	5-531020-1	OBSOLETE	8
	H	G	F	E	D	C	B	A	POSN	PART NUMBER		

6	OBSOLETE	4.100	.125	4.900	4.600	4.100	4.300	3.900	39	40/80	3-531020-4
	5	4.400	.125	5.200	4.900	4.400	4.600	4.200	42	43/86	3-531020-3
8	OBSOLETE	3.700	.125	4.500	4.200	3.700	3.900	3.500	35	36/72	3-531020-2
5	OBSOLETE	5.100	.125	5.900	5.600	5.100	5.300	4.900	49	50/100	3-531020-1
	5	6.600	0.160	7.400	7.100	6.600	6.800	6.400	64	65/160	3-531020-0
		5.100	0.160	5.900	5.600	5.100	5.300	4.900	49	50/100	2-531020-9
	5	4.400	0.160	5.200	4.900	4.400	4.600	4.200	42	43/86	2-531020-8
5	OBSOLETE	2.900	0.160	3.700	3.400	2.900	3.100	2.700	27	28/56	2-531020-7
		OBSOLETE	3.200	0.160	4.000	3.700	3.200	3.400	30	31/62	2-531020-1
		OBSOLETE	6.600	0.160	7.400	7.100	6.600	6.800	64	65/130	2-531020-0
8	OBSOLETE	6.100	0.160	6.900	6.600	6.100	6.300	5.900	59	60/120	1-531020-9
		OBSOLETE	5.100	0.160	5.900	5.600	5.100	5.300	49	50/100	1-531020-8
8	OBSOLETE	4.400	0.160	5.200	4.900	4.400	4.600	4.200	42	43/86	1-531020-7
		OBSOLETE	4.300	0.160	5.100	4.800	4.300	4.500	41	42/84	1-531020-6
		OBSOLETE	4.100	0.160	4.900	4.600	4.100	4.300	39	40/80	1-531020-5
		OBSOLETE	3.700	0.160	4.500	4.200	3.700	3.900	35	36/72	1-531020-4
8	OBSOLETE	2.900	0.160	3.700	3.400	2.900	3.100	2.700	27	28/56	1-531020-3
8	OBSOLETE	2.600	0.160	3.400	3.100	2.600	2.800	2.400	24	25/50	1-531020-2
8	OBSOLETE	2.300	0.160	3.100	2.800	2.300	2.500	2.100	21	22/44	1-531020-1
8	OBSOLETE	6.600	.125	7.400	7.100	6.600	6.800	6.400	64	65/130	1-531020-0
		OBSOLETE	6.100	.125	6.900	6.600	6.100	6.300	59	60/120	531020-9
		OBSOLETE	5.100	.125	5.900	5.600	5.100	5.300	49	50/100	531020-8
		OBSOLETE	4.400	.125	5.200	4.900	4.400	4.600	42	43/86	531020-7
		OBSOLETE	4.300	.125	5.100	4.800	4.300	4.500	41	42/84	531020-6
8	OBSOLETE	4.100	.125	4.900	4.600	4.100	4.300	3.900	39	40/80	531020-5
		OBSOLETE	3.700	.125	4.500	4.200	3.700	3.900	35	36/72	531020-4
		OBSOLETE	2.900	.125	3.700	3.400	2.900	3.100	27	28/56	531020-3
		OBSOLETE	2.600	.125	3.400	3.100	2.600	2.800	24	25/50	531020-2
8	OBSOLETE	2.300	.125	3.100	2.800	2.300	2.500	2.100	21	22/44	531020-1
		H	G	F	E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.										DWN L.WAREHAM 5-88										TE Connectivity									
										CHK D.GORENC 5-88																			
DIMENSIONS: INCHES										TOLERANCES UNLESS OTHERWISE SPECIFIED:										APVD D.GORENC 5-88									
										0 PLC ± -										NAME									
										1 PLC ± -										PRODUCT SPEC									
										2 PLC ± -										APPLICATION SPEC									
										3 PLC ± .010										SIZE CAGE CODE DRAWING NO RESTRICTED TO									
										4 PLC ± -										WEIGHT									
MATERIAL										FINISH										A2 00779 C-531020									
																				CUSTOMER DRAWING									
																				SCALE 1:1 SHEET 2 OF 2 REV AH									