


G3VM-35□G□/351VY/401G□/401VY

MOS FET Relays SOP 4-pin, General-purpose Type

General-purpose MOS FET Relays in SOP 4-pin packages for a wide range of applications

- Contact form: 1a (SPST-NO) or 1b (SPST-NC)
- Load voltage: 350 V or 400 V

RoHS Compliant



Note: The actual product is marked differently from the image shown here.

Application Examples



- Semiconductor test equipment
- Test & Measurement equipment
- Communication equipment
- Various battery-driven devices
- Security equipment
- Industrial equipment
- Power circuit
- Amusement equipment

Package

(Unit : mm, Average)

SOP 4-pin

Special SOP 4-pin



Note: The actual product is marked differently from the image shown here.

Model Number Legend

G3VM-□□□□□
1 2 3 4 5

1. Load Voltage

35 : 350 V

40 : 400 V

2. Contact form

1 : 1a (SPST-NO)

3 : 1b (SPST-NC)

3. Package

G : SOP 4-pin

V : Special SOP 4-pin

4. Additional functions

None: Dielectric strength between I/O 1500 V

Y: Dielectric strength between I/O 3750 V

5. Other informations

When specifications overlap, serial code is added in the recorded order.

Ordering Information

Package	Contact form	Terminals	Load voltage (peak value) *	Continuous load current (peak value) *	Stick packaging		Tape packaging	
					Model	Minimum package quantity	Model	Minimum package quantity
SOP4	1a (SPST-NO)	Surface- mounting Terminals	350 V	100 mA	G3VM-351G1	100 pcs.	G3VM-351G1(TR)	2,500 pcs.
Special SOP 4-PIN				110 mA	G3VM-351G		G3VM-351G(TR)	
	120 mA				G3VM-351VY	125 pcs.	G3VM-351VY(TR05)	500 pcs.
G3VM-351VY(TR)				3,000 pcs.				
SOP4	1b (SPST-NC)		400 V	120 mA	G3VM-353G	100 pcs.	G3VM-353G(TR)	2,500 pcs.
	1a (SPST-NO)			100 mA	G3VM-401G1		G3VM-401G1(TR)	
				120 mA	G3VM-401G		G3VM-401G(TR)	
Special SOP 4-PIN				110mA	G3VM-401VY	125 pcs.	G3VM-401VY(TR05)	500 pcs.

* The AC peak and DC value are given for the load voltage and continuous load current.

Note: To order tape packaging for Relays with surface-mounting terminals, add "(TR)", "(TR05)" to the end of the model number.

■Absolute Maximum Ratings (Ta = 25°C)


Item		Symbol	G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit	Measurement conditions
Input	LED forward current	IF	50		30	50	30	50	30	mA	
	LED forward current reduction rate	ΔIF/°C	-0.5		-0.3	-0.5	-0.3	-0.5	-0.3	mA/°C	Ta ≥ 25°C
	LED reverse voltage	VR	5		6	5			6	V	
	Connection temperature	TJ	125							°C	
Output	Load voltage (AC peak/DC)	VOFF	350				400			V	
	Continuous load current (AC peak/DC)	Io	100	110		120	100	120	110	mA	
	ON current reduction rate	ΔIo/°C	-1.0	-1.1		-1.2	-1.0	-1.2	-1.1	mA/°C	Ta ≥ 25°C
	Pulse ON current	Iop	300	330		360	300	360	330	mA	t=100 ms, Duty=1/10
	Connection temperature	TJ	125							°C	
	Dielectric strength between I/O *	VI-O	1500		3750	1500			3750	Vrms	AC for 1 min
Ambient operating temperature		Ta	-40 to +85		-40 to +110	-40 to +85			-40 to +110	°C	With no icing or condensation
Ambient storage temperature		Tstg	-55 to +125							°C	
Soldering temperature		—	260							°C	

* The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■Electrical Characteristics (Ta = 25°C)

Item			Symbol	G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit	Measurement conditions	
Input	LED forward voltage	V _F	Minimum	1.0		1.1	1.0	1.1	1.0	1.1	V	I _F =10 mA	
			Typical	1.15		1.27	1.15	1.27	1.15	1.27			
			Maximum	1.3		1.4	1.3	1.4	1.3	1.4			
	Reverse current	I _R	Maximum	10								μA	V _R =5 V
	Capacitance between terminals	C _T	Typical	30								pF	V=0, f=1 MHz
	Trigger LED forward current	I _{FT} (I _{FC}) *2	Typical	0.4	1	0.8	1	—	1	0.8	mA	G3VM-351G1/351G/401G1 : I _o =100 mA G3VM-351VY/401VY : I _o =110 mA G3VM-353G : I _{OFF} =10 μA G3VM-401G : I _o =120 mA	
			Maximum	1	3			0.2	3				
Release LED forward current	I _{FC} (I _{FT}) *2	Minimum	0.1				—	0.1		mA	G3VM-351G1/351VY/351G/401G1/401G/401VY : I _{OFF} =100 μA G3VM-353G : I _o =120 mA		
		Typical	—		0.4	—	0.001	—	0.5				
Output	Maximum resistance with output ON	R _{ON}	Typical	35 (25)		35 (22)	15	18	17	40 (30)	Ω	G3VM-351G1 : I _F =2 mA, I _o =100 mA Values in parentheses are for t < 1 s. G3VM-351G : I _F =5 mA, I _o =110 mA Values in parentheses are for t < 1 s. G3VM-351VY/401VY: I _F =5 mA, I _o =110 mA Values in parentheses are for t < 1 s. G3VM-353G : I _o =120 mA G3VM-401G1 : I _F =0.5 mA, I _o =100 mA, t < 1 s G3VM-401G : I _F =5 mA, I _o =120 mA	
			Maximum	50 (35)			25	35		65 (45)			
	Current leakage when the relay is open	I _{LEAK}	Typical	1	—	1	—	1	—	1	nA	G3VM-351G1/351VY/351G : V _{OFF} =350 V G3VM-353G : V _{OFF} =350 V, I _F =5 mA G3VM-401G1/401G/401VY : V _{OFF} =400 V	
			Maximum	1,000									
	Capacitance between terminals	C _{OFF}	Typical	35	30	30	65	70		30	pF	G3VM-351G1/351VY/351G/401G1/401G/401VY : V=0, f=1 MHz G3VM-353G : V=0, f=1 MHz, I _F =5 mA	
Capacitance between I/O terminals	C _{I-O}	Typical	0.8								pF	f=1 MHz, V _S =0 V	
Insulation resistance between I/O terminals	R _{I-O}	Minimum	1000								MΩ	V _{I-O} =500 VDC, R _{oH} ≤60%	
		Typical	10 ⁸										
Turn-ON time	t _{ON}	Typical	1	0.3	0.5	—	2	0.3	0.5	ms	G3VM-351G1 : I _F =2 mA, R _L =200 Ω, V _{DD} =20 V G3VM-401G1 : I _F =0.5 mA, R _L =200 Ω, V _{DD} =20 V Others : I _F =5 mA, R _L =200 Ω, V _{DD} =20 V *1		
		Maximum	5	1			10	1					
Turn-OFF time	t _{OFF}	Typical	1	0.1		—	1	0.1					
		Maximum	3	1	0.5	3	5	1	0.5				

*1. Turn-ON and Turn-OFF Times



*2. These values are for Relays with NC contacts

Recommended Operating Conditions

For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.

Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.


Item	Symbol		G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit
Load voltage (AC peak/DC)	V _{DD}	Maximum	280				320			V
Operating LED forward current	I _F	Minimum	–	5		–	5		mA	
		Typical	2	7.5		–	0.5	7.5		
		Maximum	25							
Continuous load current (AC peak/DC)	I _O	Maximum	80	100	110	120	80	120	110	°C
Ambient operating temperature	T _a	Minimum	-20							
		Maximum	65		100	65			100	

Spacing and Insulation


Item	G3VM-35□G□/401G□	G3VM-351VY/401VY	Unit
	Minimum		
Creepage distances	4.0	5.0	mm
Clearance distances	4.0	5.0	
Internal isolation thickness	0.1	0.2	

Engineering Data


LED forward current vs. Ambient temperature



Continuous load current vs. Ambient temperature




LED forward current vs. LED forward voltage




Continuous load current vs. On-state voltage

G3VM-351G/351G1/353G




G3VM-351VY/401G/401G1/401VY




On-state resistance vs. Ambient temperature


G3VM-351G/351G1/353G



G3VM-351VY/401G/401G1/401VY




Trigger LED forward current vs. Ambient temperature




Turn ON, Turn OFF time vs. LED forward current

G3VM-351G/351G1/353G




G3VM-351VY/401G/401G1/401VY




Engineering Data


● Turn ON, Turn OFF time vs. Ambient temperature G3VM-351G/351G1/353G




G3VM-351VY/401G/401G1/401VY




● Current leakage vs. Ambient temperature G3VM-351G/351G1/353G/351VY/ 401G/401G1



G3VM-401VY



● Current leakage vs. Load voltage




■Appearance / Terminal Arrangement / Internal Connections


●Appearance

SOP (Small Outline Package)

SOP 4-pin



Special SOP 4-pin (G3VM-351VY/401VY)



Note: 1. The actual product is marked differently from the image shown here.


Note: 2. "G3VM" does not appear in the model number on the Relay.

Note: 3. The indentation in the corner diagonally opposite from the pin 1 mark is from a pin on the mold.


●Terminal Arrangement/Internal Connections (Top View)

G3VM-351G1/G/VY

G3VM-401G1/G/VY



G3VM-353G



■Dimensions (Unit: mm)


SOP (Small Outline Package)

SOP 4-pin




Surface-mounting Terminals

Weight: 0.1 g




Actual Mounting Pad Dimensions

(Recommended Value, Top View)




Note: The actual product is marked differently from the image shown here.

Special SOP 4-pin * (G3VM-351VY/401VY)




Surface-mounting Terminals

Weight: 0.1 g



Actual Mounting Pad Dimensions

(Recommended Value, Top View)



* The external dimensions are different from those of the standard SOP 4-pin, but the mounting pad dimensions are the same.

Note: The actual product is marked differently from the image shown here.

■Approved Standards

UL recognized



Model	Approved Standards	Contact form	File No.
G3VM-351G1 G3VM-351G G3VM-401G G3VM-351VY G3VM-401VY	UL (recognized)	1a (SPST-NO)	E80555
G3VM-353G		1b (SPST-NC)	

Models Certified by BSI for EN/IEC Standards

Model	Approved Standards	Contact form	File No.
G3VM-401G	EN62368-1 (BSI certified)	1a (SPST-NO)	VC669262

■Safety Precautions

- Refer to the *Common Precautions for All MOS FET Relays* for precautions that apply to all MOS FET Relays.

SOP

G3VM-35□G□/351VY/401G□/401VY

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Electronic and Mechanical Components Company

Regional Contact

Americas

<https://www.components.omron.com/>

Asia-Pacific

<https://ecb.omron.com.sg/>

Korea

<https://www.omron-ecb.co.kr/>

Europe

<http://components.omron.eu/>

China

<https://www.ecb.omron.com.cn/>

Japan

<https://www.omron.co.jp/ecb/>