




PLETRONICS OSJ7014-10.0M OCXO Oscillator



OSJ7 Series
25.4 x 22.1 x 12.2 mm
7 Pad SMD Package

Features

- Ovenized High Precision Quartz Crystal Oscillator
- Sinewave
- 3.3V nominal Supply Voltage
- 10.0 MHz Nominal Frequency
- SC cut crystal

Electrical Characteristics

Parameter	Min	Typ	Max	Unit	Condition
Frequency	-	10.0	-	MHz	
Initial Accuracy	-	-	±0.2	ppm	@+25 ± 1°C after turn on power 15 ± 1 minutes ≤90 days following date code, Vc = 1.65V ± 0.001V
Frequency Stability vs Temperature	-	-	±10	ppb	-20 to +70°C, referenced to 25°C
Frequency Stability vs Supply	-	-	±2	ppb	±5% voltage change
Frequency Stability Vs Load			±2	ppb	±5%
Short term	-	0.01	-	ppb/s	root Allan variance
Warm-up	-	-	±100	ppb	In 5 minutes @ +25°C, referenced to 1 hour
Aging	-	-	±1	ppb	per day, after 30 days
	-	-	±50	ppb	per year
	-	-	±0.3	ppm	20 years
Operating Temperature Range	-20	-	+70	°C	
Supply Voltage ¹ V _{CC}	3.135	3.3	3.465	V	
Power - Turn-on	-	-	3.2	W	@ turn on
Power - Steady State	-	-	1.15	W	@ 25°C
Voltage Control Vc	0.3	1.65	3.0	V	
Vc Input Impedance	50	-	-	kΩ	
Pullability	±0.5	-	-	ppm	
Linearity	-	-	±10	%	Positive slope
Phase Noise	1 Hz 10 Hz 100 Hz 1 kHz 10 kHz 100 kHz	-85 -115 -140 -145 -150 -150	-	dBc/Hz	
Storage Temperature Range	-55	-	+125	°C	

Output Characteristics

Parameter	Min	Typ	Max	Unit	Condition
Output Waveform	Sinewave				
Output Load	-	50	-	Ω	
Output Level	+5	-	-	dBm	
Harmonic	-	-	-30	dBc	
Spurious	-	-	-80	dBc	
Startup time	-	-	0.5	s	

Note: ¹ Place a 10nF power supply bypass capacitor next to device for correct operation



PLETRONICS OSJ7014-10.0M OCXO Oscillator

Device Marking

PLE
OSJ7014
10.0M
YMDz
S/N: xxx

PLE = Pletronics
OSJ7014 = Model number/Part number
10.0M = Frequency (M = MHz)
YMD = Date code (Year-Month-Day: See Table below)
z = Internal Factory Code
S/N: xxx = Serial number

Specifications such as part number, frequency stability, supply voltage and operating temperature range, etc. are not identified from marking. External packaging labels and packing list will correctly identify the ordered Pletronics part number.

Codes for Date Code YMD (Year Month Day)

Code	2	3	4	5	6	Code	A	B	C	D	E	F	G	H	J	K	L	M
Year	2022	2023	2024	2025	2026	Month	JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC

Code	1	2	3	4	5	6	7	8	9	A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	T	U	V	W	X	Y	Z
Day	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31

Package Labeling

P/N Label is 1" x 2.6" (25.4mm x 66.7mm)
Font is Courier New
Bar code is 39-Full ASCII



RoHS Label is 1" x 2.6" (25.4mm x 66.7mm)
Font is Arial

RoHS Compliant

2nd Lvl Interconnect

Category=e4

Max Safe Temp=245C for 10s 2X Max

Pletronics Inc. certifies this device is in accordance with the RoHS (exemptions 6c, 7c-i) and REACH directives.
Pletronics Inc. guarantees the device does not contain the following: Cadmium, Hexavalent Chromium, Mercury, PBB's, PBDE's
Moisture Sensitivity Level: 1 As defined in J-STD-020D
Second Level Interconnect code: e4

Environmental / ESD Ratings


Reliability: Environmental

Parameter	Ref Standard	Condition
Solderability	MIL-STD-202, Method 208	
Mechanical Shock (non-operating)	MIL-STD-202, Method 213 Test Cond J	30g, 11ms, half-sine
Vibration (non-operating)	MIL-STD-202, Method 201	0.06" Total p-p, 10 to 55 Hz
Thermal Shock	MIL-STD-202, Method 107 Test Cond B	5 cycles -65 to +125 Deg C
Humidity	MIL-STD-202, Method 103, Test Condition A	95% RH @ +40°C, non-condensing, 240 hours


Parameter	Condition
Cleaning	Aqueous cleaning is FORBIDDEN
Reflow	Bottom side assembly is FORBIDDEN

Mechanical Dimensions

TOP VIEW




Pin Connections	
PIN	FUNCTION
1	Vc Input
2	Not Connected
3	+VDC
4	R.F. Output
5	Not Connected
6	Not Connected
7	0 Volts & Case



Note 1: Copper in this area should be kept to a minimum to reduce heat loss from the OCXO.


Note 2: Consult oscillator specification for exposed OCXO copper in this area.

Recommended solder pad layout



BOTTOM VIEW

See note 1+2




INCH
mm (reference only)

For Optimum Jitter Performance, Pletronics recommends:

- A ground plane under the device
- Do not route large transient signals (both current and voltage) under the device
- Do not place near a large magnetic field such as a high frequency switching power supply
- Do not place near piezoelectric buzzers or mechanical fans
- Minimize air flow across the device

Reflow Cycle



Maximum Reflow Conditions in accordance with IPC/JEDEC J-STD-020C "Pb-free"



Temperature Profile	Symbol	Condition	Unit
Average ramp-up rate	$(T_{smax} \text{ to } T_P)$	3°C / second max	°C / s
Ramp down Rate	T_{cool}	6°C / second max	°C / s
Time 25°C to Peak Temperature	$T_{to-peak}$	8 minutes max	min
Preheat			
Temperature min	T_{smin}	150	°C
Temperature max	T_{smax}	200	°C
Time T_{smin} to T_{smax}	t_s	60 – 180	sec
Soldering above liquidus			
Temperature liquidus	T_L	217	°C
Time above liquidus	t_L	60 – 150	sec
Peak temperature			
Peak Temperature	T_P	260	°C
Time within 5°C of peak temperature	t_P	20 – 40	sec

Tape and Reel

Tape and Reel available for quantities of 200, cut tape for < 200. 44mm tape, 32mm pitch.



Tape Variable Dimensions Table 2

Tape Size	E2 typ	F	P1	W max	Ao	Bo	Ko
44mm	40.4	20.2 ± 0.15	32.0 ± 0.1	44.3	23 ± 0.1	26 ± 0.1	12.5 ± 0.1

Dimensions in mm Drawing Not to scale

Note 1: Embossed cavity to conform to EIA- 481-B

Tape Constant Dimensions Table 1

Tape Size	Do	D1	E1	Po	P2	t max
44mm	1.5 $+0.1$ -0.0	2.0 ± 0.1	1.75 ± 0.1	4.0 ± 0.1	2.0 ± 0.05	0.55

Reel Dimensions (may vary) Table 3

	A		B		C	D
Reel Size	Inches	mm	Inches	mm	mm	mm
13	13.0	330.2	3.94	100	13.0 $+0.5$ -0.2	44.4 $+2.0$ -0.0



Important Notice

Pletronics Incorporated (PLE) reserves the right to make corrections, improvements, modifications and other changes to this product at anytime. PLE reserves the right to discontinue any product or service without notice. Customers are responsible for obtaining the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to PLE's terms and conditions of sale supplied at the time of order acknowledgment.

PLE warrants performance of this product to the specifications applicable at the time of sale in accordance with PLE's limited warranty. Testing and other quality control techniques are used to the extent PLE deems necessary to support this warranty. Except where mandated by specific contractual documents, testing of all parameters of each product is not necessarily performed.

PLE assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using PLE components. To minimize the risks associated with the customer products and applications, customers should provide adequate design and operating safeguards.

PLE products are not designed, intended, authorized or warranted to be suitable for use in life support applications, weapons, weapon systems or space applications, devices or systems or other critical applications that may involve potential risks of death, personal injury or severe property or environmental damage. Inclusion of PLE products in such applications is understood to be fully at the risk of the customer. Use of PLE products in such applications requires the written approval of an appropriate PLE officer. Questions concerning potential risk applications should be directed to PLE.

PLE does not warrant or represent that any license, either express or implied, is granted under any PLE patent right, copyright, artwork or other intellectual property right relating to any combination, machine or process which PLE product or services are used. Information published by PLE regarding third-party products or services does not constitute a license from PLE to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from PLE under the patents or other intellectual property of PLE.

Reproduction of information in PLE data sheets or web site is permissible only if the reproduction is without alteration and is accompanied by associated warranties, conditions, limitations and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. PLE is not responsible or liable for such altered documents.

Resale of PLE products or services with statements different from or beyond the parameters stated by PLE for that product or service voids all express and implied warranties for the associated PLE product or service and is an unfair or deceptive business practice. PLE is not responsible for any such statements.

Contacting Pletronics Inc.

Pletronics, Inc.
19013 36th Ave. West
Lynnwood, WA 98036-5761
U.S.A.

Tel: 425.776.1880
Fax: 425.776.2760
email: ple-sales@pletronics.com

URL: www.pletronics.com