



THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND ITS SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

DATE	REV	REVISION RECORD	APP	DR	CK
8-16 04	B	ECO 22872	RCW	YK	TK
10-21 16	C	ECO 53048	CM	CM	CM



NOTES:

1. MATERIALS AND FINISHES:
CONTACT: PRECISION-MACHINED COPPER ALLOY WITH GOLD FLASH OVER NICKEL PLATE.
RETENTION RING: POLYETHERIMIDE, COLOR BLACK.
2. ELECTRICAL CHARACTERISTICS:
CONTACT CURRENT RATING: 60 AMPERES, CONTINUOUS.
INITIAL CONTACT RESISTANCE: 0.005 OHMS MAXIMUM.
3. FOR USE WITH 9509-0-0-0 CRIMP TOOL.
4. DIMENSIONS ARE IN MILLIMETERS [INCHES].



POSITRONIC
INDUSTRIES INC.

SPRINGFIELD, MISSOURI 65801

SCALE	DRAWN BY	Y. KELLEYBREW
CBD SERIES	N.T.S.	APPROVED BY
DECIMAL TOL.		RCW
± 0.38 [0.015]		
ANGULAR TOL.	DRAWING NUMBER	REV.
± 5°	10-19-00	C

FC4010D

SK3456