


Test Voltage Range	5V~30V DC
Insulation Resistance	DC 500V 100M Ω Min
Dielectric Strength	AC 1500V 1 Second
Operating Temperature	-0°C~+40°C
Voltage Tolerance	$\pm 0.2V$ DC



A4

									$\triangle$
									$\triangle$
Date	Name	Description							NO
Drawn	Checked	Approved	SCI BOM No.		Model Name	Battery Tester			
胡朝鈺			Customer No.	112-R8-124BP	Model No.	R8-124BP			REV.
8/10/2009		8/19/09	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.				0