


RF_35/05.10/6.0 Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

Technical Data Sheet		Rosenberger
RPC 2.92	Straight Jack PCB Solderless compression	R02K709-500S3



DETAIL X

All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to
Mechanically compatible with

IEC 61169-35
RPC-3.50 and SMA

Documents

N/A

Material and plating

Connector parts

Center contact
Outer contact
Dielectric
Screw

Material

CuBe
Stainless steel
PEEK
Stainless steel

Plating

AuroDur®, gold plated
Passivated

Passivated

Rosenberger Hochfrequenztechnik GmbH & Co. KG Tel.: +49 8684 18-0 www.rosenberger.de	Fax: +49 8684 18-499 email : info@rosenberger.de	Rosenberger Asia Pacific Electronic Co., Ltd., China Tel.: +86 10 80481995 www.rosenbergerap.com	Fax: +86 10 80497052 email: info@rosenbergerap.com	Page 1 / 2
--	--	---	---	-------------------

RF_35/05.10/6.0 Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

Technical Data Sheet					Rosenberger					
RPC 2.92		Straight Jack PCB Solderless compression			R02K709-500S3					
Electrical data										
Impedance		50 Ω								
Frequency		DC to 40 GHz								
Return loss		≥ 17 dB								
Insertion loss		≤ 0.06 dB								
Insulation resistance		≥ 5 x10 ³ MΩ								
Center contact resistance		≤ 3.0 mΩ								
Outer contact resistance		≤ 2.0 mΩ								
Test voltage		750 V rms								
Working voltage		250 V rms								
RF-leakage		≥100 dB up to 1 GHz								
Mechanical data										
Mating cycles		≥ 500								
Center contact captivation		axial: ≥ 20 N								
		radial: ≥ 1 Ncm								
Coupling test torque		≤ 1.7 Nm								
Recommended torque		0.8 Nm to 1.1 Nm								
Environmental data										
Temperature range		-45°C to +125°C								
Thermal shock		MIL-STD-202, Method 107, Condition B								
Corrosion resistance		MIL-STD-202, Method 101, Condition B								
Vibration		MIL-STD-202, Method 204, Condition D								
Shock		MIL-STD-202, Method 213, Condition I								
Moisture resistance		MIL-STD-202, Method 106,								
RoHS		compliant								
Accessories										
		N/A								
Tooling										
		N/A								
Packing										
Weight		2 g/pce								
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.										
Draft	Date	Checked	Approved	Date	Rev.	Engineering change number	Name	Date		
zoufh	17.06.20	xibinhong	heanyang	17.06.20	100	/	zoufh	17.06.20		
Rosenberger Hochfrequenztechnik GmbH & Co. KG Tel.: +49 8684 18-0 Fax: +49 8684 18-499 www.rosenberger.de email : info@rosenberger.de					Rosenberger Asia Pacific Electronic Co., Ltd., China Tel.: +86 10 80481995 Fax: +86 10 80497052 www.rosenbergerap.com email: info@rosenbergerap.com					Page 2 / 2