



Rosenberger

Vertical Male PCB Connector

W2S101-40ML3-XX

W2S101-40ML3-16



PROPRIETARY AND CONFIDENTIAL

THIS DATA SHEET IS THE PROPERTY OF ROSENBERGER NORTH AMERICA AKRON, LLC. BY ACCEPTANCE OF THIS DOCUMENT, YOU AGREE THAT ALL THE RIGHTS TO DRAWINGS, SPECIFICATIONS, PROCESSES, AND OTHER DATA THEREIN, AS WELL AS THE PROPRIETARY AND NOVEL FEATURES OF THE SUBJECT MATTER, ARE RESERVED BY ROSENBERGER NORTH AMERICA AKRON, LLC, AND ARE DISCLOSED IN CONFIDENCE. THEY ARE NOT TO BE MANUFACTURED, USED, SOLD, OR DISCLOSED TO OTHERS, NOR ARE DEVICES EMBODYING SUCH FEATURES OR INFORMATION DERIVED FROM THESE DISCLOSURES TO BE USED OR DISCLOSED UNLESS NOTED AND NOT EXPRESSLY AUTHORIZED BY ROSENBERGER NORTH AMERICA AKRON, LLC. THESE DRAWINGS, SPECIFICATIONS, PROCESSES, ETC., ARE AND REMAIN THE PROPERTY OF ROSENBERGER NORTH AMERICA AKRON, LLC, AND ARE NOT TO BE COPIED OR REPRODUCED WITHOUT PERMISSION.

FR-053
RNA Datasheet2 Rev A
08/01/2022



Rosenberger North America Akron, LLC
P.O. Box 309 Akron, PA USA 17501
www.rosenbergerna.com

Tel. : +1.717.859.8900
Fax : +1.717.859.7044
Email : info@rosenbergerna.com

Page
1 / 6

PROPRIETARY AND CONFIDENTIAL
This data sheet is the property of Rosenberg North America Akron, LLC. By acceptance of this document, you agree that all the rights to drawings, specifications, processes, and other data therein, as well as the proprietary and novel features of the subject matter, are reserved by Rosenberg North America Akron, LLC, and are disclosed in confidence. They are not to be manufactured, used, sold, or disclosed to others, nor are devices embodying such features or information derived from these disclosures to be used or disclosed unless and until expressly authorized by Rosenberg North America Akron, LLC. These drawings, specifications, processes, etc., are and remain the property of Rosenberg North America Akron, LLC, and are not to be copied or reproduced without permission.

FR-053
RNA Datasheet2 Rev A
08/01/2022

Technical Data Sheet		Rosenberger
SMPX	Vertical Male PCB Connector	W2S101-40ML3-XX
W2S101-40ML3-08  STIFFENER (OPTIONAL) 4X M1 X 4mm 		
Rosenberger North America Akron, LLC P.O. Box 309 Akron, PA USA 17501 www.rosenbergerna.com		Tel. : +1.717.859.8900 Fax : +1.717.859.7044 Email : info@rosenbergerna.com
		Page 2 / 6

Technical Data Sheet



Rosenberger

SMPX


Vertical Male PCB Connector

W2S101-40ML3-XX

W2S101-40ML3-04



W2S101-40ML3-02



All dimensions are in mm

Unless otherwise specified tolerances are as follows: .XX±.025; XXX±.012

PROPRIETARY AND CONFIDENTIAL
This data sheet is the property of Rosenberger North America Akron, LLC. By acceptance of this document, you agree that all the rights to drawings, specifications, processes, and other data therein, as well as the proprietary and novel features of the subject matter, are reserved by Rosenberger North America Akron, LLC, and are disclosed in confidence. They are not to be manufactured, used, sold, or disclosed to others, nor are devices embodying such features or information derived from these disclosures to be used or disclosed unless and until expressly authorized by Rosenberger North America Akron, LLC. These drawings, specifications, processes, etc., are and remain the property of Rosenberger North America Akron, LLC, and are not to be copied or reproduced without permission.

FR-053
RNA DataSheet2 Rev A
08/01/2022

Rosenberger North America Akron, LLC
P.O. Box 309 Akron, PA USA 17501
www.rosenbergerna.com

Tel. : +1.717.859.8900
Fax : +1.717.859.7044
Email : info@rosenbergerna.com

Page
3 / 6

Technical Data Sheet		Rosenberger																																																															
SMPX	Vertical Male PCB Connector	W2S101-40ML3-XX																																																															
Interface According to Rosenberger SMPX Interface standards Material and plating <table><tr><th>Connector parts</th><th>Material</th><th>Plating</th></tr><tr><td>Body</td><td>Brass per ASTM B16</td><td>Hard Gold, 6µin min over Electroless Nickel, 80µin min</td></tr><tr><td>Pin</td><td>CuBe per ASTM B196</td><td>Hard Gold, 31µin min over Electroless Nickel, 80µin min</td></tr><tr><td>Front Insulator</td><td>ULTEM® 1000 or equivalent per ASTM D5205, PEI0113</td><td></td></tr><tr><td>Back Insulator</td><td>PEEK 1000 or equivalent Per ASTM 6262</td><td></td></tr><tr><td>Stiffener (Optional)</td><td>SST per ASTM A582</td><td>Passivated</td></tr><tr><td>M1 X 4mm Screw*</td><td>SST per ASTM A582</td><td>Passivated</td></tr></table> *Note: The screw sizes can be modified to accommodate variations in board thickness. The screw sizes listed above allow for board thickness of X.XX ± X.XX Electrical data (@ STP unless otherwise specified) <table><tr><td>Impedance</td><td>50 Ω</td></tr><tr><td>Frequency</td><td>DC to 110 GHz</td></tr><tr><td>Return Loss*</td><td>≤ 15 dB at 70 GHz</td></tr><tr><td>Insertion loss</td><td>≤ 0.1 dB x √f(GHz), DC to 70 GHz</td></tr><tr><td>Insulation resistance</td><td>≥ 5 GΩ</td></tr><tr><td>Center contact resistance</td><td>≤ xx mΩ</td></tr><tr><td>Outer contact resistance</td><td>≤ xx mΩ</td></tr><tr><td>Working Voltage</td><td>500 V rms</td></tr><tr><td>RF High Potential</td><td>xxx V rms @ 5 MHz</td></tr><tr><td>RF leakage</td><td>≥ xx dB</td></tr></table> Mechanical data <table><tr><td>Mating cycles (single channel)</td><td>≤ 10000</td></tr><tr><td>Engagement force (max)</td><td>0.9 lbf [4.0 N]</td></tr><tr><td>Disengagement force (min)</td><td>1.32 lbf [5.9 N]</td></tr><tr><td>PCB Installation Cycles</td><td>100 (Typical)</td></tr></table> Environmental data <table><tr><td>Temperature range</td><td>-40°C to +120°C</td></tr><tr><td>Thermal shock</td><td>MIL-STD-202 – 107, Condition B</td></tr><tr><td>Corrosion</td><td>MIL-STD-202 – 101, Condition B</td></tr><tr><td>Vibration</td><td>MIL-STD-202 – 204, Condition B</td></tr><tr><td>Shock</td><td>MIL-STD-202 – 213, Condition A</td></tr><tr><td>Moisture resistance</td><td>MIL-STD-202 – 106, except Step 7B</td></tr><tr><td>2002/95/EC (RoHS)</td><td>compliant</td></tr></table>			Connector parts	Material	Plating	Body	Brass per ASTM B16	Hard Gold, 6µin min over Electroless Nickel, 80µin min	Pin	CuBe per ASTM B196	Hard Gold, 31µin min over Electroless Nickel, 80µin min	Front Insulator	ULTEM® 1000 or equivalent per ASTM D5205, PEI0113		Back Insulator	PEEK 1000 or equivalent Per ASTM 6262		Stiffener (Optional)	SST per ASTM A582	Passivated	M1 X 4mm Screw*	SST per ASTM A582	Passivated	Impedance	50 Ω	Frequency	DC to 110 GHz	Return Loss*	≤ 15 dB at 70 GHz	Insertion loss	≤ 0.1 dB x √f(GHz), DC to 70 GHz	Insulation resistance	≥ 5 GΩ	Center contact resistance	≤ xx mΩ	Outer contact resistance	≤ xx mΩ	Working Voltage	500 V rms	RF High Potential	xxx V rms @ 5 MHz	RF leakage	≥ xx dB	Mating cycles (single channel)	≤ 10000	Engagement force (max)	0.9 lbf [4.0 N]	Disengagement force (min)	1.32 lbf [5.9 N]	PCB Installation Cycles	100 (Typical)	Temperature range	-40°C to +120°C	Thermal shock	MIL-STD-202 – 107, Condition B	Corrosion	MIL-STD-202 – 101, Condition B	Vibration	MIL-STD-202 – 204, Condition B	Shock	MIL-STD-202 – 213, Condition A	Moisture resistance	MIL-STD-202 – 106, except Step 7B	2002/95/EC (RoHS)	compliant
Connector parts	Material	Plating																																																															
Body	Brass per ASTM B16	Hard Gold, 6µin min over Electroless Nickel, 80µin min																																																															
Pin	CuBe per ASTM B196	Hard Gold, 31µin min over Electroless Nickel, 80µin min																																																															
Front Insulator	ULTEM® 1000 or equivalent per ASTM D5205, PEI0113																																																																
Back Insulator	PEEK 1000 or equivalent Per ASTM 6262																																																																
Stiffener (Optional)	SST per ASTM A582	Passivated																																																															
M1 X 4mm Screw*	SST per ASTM A582	Passivated																																																															
Impedance	50 Ω																																																																
Frequency	DC to 110 GHz																																																																
Return Loss*	≤ 15 dB at 70 GHz																																																																
Insertion loss	≤ 0.1 dB x √f(GHz), DC to 70 GHz																																																																
Insulation resistance	≥ 5 GΩ																																																																
Center contact resistance	≤ xx mΩ																																																																
Outer contact resistance	≤ xx mΩ																																																																
Working Voltage	500 V rms																																																																
RF High Potential	xxx V rms @ 5 MHz																																																																
RF leakage	≥ xx dB																																																																
Mating cycles (single channel)	≤ 10000																																																																
Engagement force (max)	0.9 lbf [4.0 N]																																																																
Disengagement force (min)	1.32 lbf [5.9 N]																																																																
PCB Installation Cycles	100 (Typical)																																																																
Temperature range	-40°C to +120°C																																																																
Thermal shock	MIL-STD-202 – 107, Condition B																																																																
Corrosion	MIL-STD-202 – 101, Condition B																																																																
Vibration	MIL-STD-202 – 204, Condition B																																																																
Shock	MIL-STD-202 – 213, Condition A																																																																
Moisture resistance	MIL-STD-202 – 106, except Step 7B																																																																
2002/95/EC (RoHS)	compliant																																																																
Rosenberger North America Akron, LLC P.O. Box 309 Akron, PA USA 17501 www.rosenbergerna.com		Tel. : +1.717.859.8900 Fax : +1.717.859.7044 Email : info@rosenbergerna.com																																																															
		Page 4 / 6																																																															

Technical Data Sheet

Rosenberger


SMPX

Vertical Male PCB Connector


W2S101-40ML3-XX

PCB Footprint

W2S101-40ML3-16



W2S101-40ML3-08



PROPRIETARY AND CONFIDENTIAL
This data sheet is the property of Rosenberger North America Akron, LLC. By acceptance of this document, you agree that all the rights to drawings, specifications, processes, and other data therein, as well as the proprietary and novel features of the subject matter, are reserved by Rosenberger North America Akron, LLC, and are disclosed in confidence. They are not to be manufactured, used, sold, or disclosed to others, nor are devices embodying such features or information derived from these disclosures to be used or disclosed unless and until expressly authorized by Rosenberger North America Akron, LLC. These drawings, specifications, processes, etc., are and remain the property of Rosenberger North America Akron, LLC, and are not to be copied or reproduced without permission.

Technical Data Sheet


Rosenberger

SMPX


Vertical Male PCB Connector

W2S101-40ML3-XX

W2S101-40ML3-04



W2S101-40ML3-02



PROPRIETARY AND CONFIDENTIAL
 This data sheet is the property of Rosenberger North America Akron, LLC. By acceptance of this document, you agree that all the rights to drawings, specifications, processes, and other data therein, as well as the proprietary and novel features of the subject matter, are reserved by Rosenberger North America Akron, LLC, and are disclosed in confidence. They are not to be manufactured, used, sold, or disclosed to others, nor are devices embodying such features or information derived from these disclosures to be used or disclosed unless and until expressly authorized by Rosenberger North America Akron, LLC. These drawings, specifications, processes, etc., are and remain the property of Rosenberger North America Akron, LLC, and are not to be copied or reproduced without permission.

FR-053
 RNA Datasheet2 Rev A
 08/01/2022

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
L. Weber	9/14/2023	E. Soubh	10/11/2023	201	Updated to SMPX	D.Hoeschen	10/28/2024
Rosenberger North America Akron, LLC P.O. Box 309 Akron, PA USA 17501 www.rosenbergerna.com				Tel. : +1.717.859.8900 Fax : +1.717.859.7044 Email : info@rosenbergerna.com			Page 6 / 6