



Satellite IoT D2D Ready

TN & NTN Dual-Mode Antenna - Satellite IoT Direct to Device Ready

Direct Mount Single Port 3G/4G Antenna

Covering 4G/5G/Satellite Band 25

The L001254-01 direct to device (D2D) antenna is a multi-band low profile disk/puck antenna operating over the 698-960 MHz and 1710-2700 MHz frequency bands.

Designed to be a surface mount antenna that performs well on metallic and non-metallic surfaces, the antenna is ideal for use in Machine-to-Machine (M2M) applications. The housing incorporates a low profile, rugged design that conforms to IP67 standards making the antenna suitable for both indoor and outdoor applications.


SATELLITE IOT D2D COMMUNICATIONS

Low Earth Orbit (LEO) satellites, positioned a few hundred km's above Earth, orbit rapidly and are ideal for IoT networks. A LEO satellite constellation can now support low data rate communications through specific LTE frequencies.

- Dual-mode capable - Supporting Terrestrial Networks (TN) and Non-Terrestrial Networks (NTN) from a single antenna
 - 698-3800 MHz terrestrial cellular coverage
 - Band 25 (1900 MHz) cellular satellite coverage
 - Testing available for other/future cellular satellite D2D frequency bands used by various network providers
- Enabling dual-mode communications via IoT devices
 - Prioritizing terrestrial networks but capable of automatically switching to satellite when the signal is weak or unavailable

REFERENCE SIGNAL RECEIVED POWER (RSRP) VALUES

The L001254-01 antenna was live-tested for receive signal strength. Data encompasses multiple satellite pass-overs, showing signal strength variation; exceeding the -120 dBm minimum for IoT devices.



An RSRP value of -120 dBm is generally the recognized minimum requirement suitable for the data rates of SMS, CAT-1, CAT-1 Bis connectivity.

RSRP can be susceptible to fluctuations for a variety of reasons. These can include: satellite elevation angle; antenna radiation patterns; solar flares; atmospheric conditions, and more.

FEATURES AND BENEFITS

- Validated for use on satcom D2D networks
- Dual-Mode TN and NTN capable
- Low profile, aesthetically-neutral housing
- Surface mount with stud and locking nut
- Designed for both indoor and outdoor use
- IP67-rated for harsh environments
- Both 3G/4G LTE and Wi-Fi communications
- Made for both metal and non-metallic surfaces

APPLICATIONS

- Non-Terrestrial and Terrestrial Networks
- Satellite IoT D2D (Direct to Device) applications
- Worldwide 5G/4G/3G/2G
- Cellular IoT: LTE-M (Cat-M1) and NB-IoT
- Remote control, monitoring and sensing
- Internet of Things (IoT) devices

SPECIFICATIONS

ELECTRICAL SPECIFICATION								
Frequency Band (MHz)	698-806	824-894	880-960	1710-1880	1850-1990	1910-2170	2300-2500	2500-2700
VSWR (Typ)	<2.7:1	<2.9:1	<2.8:1	<2.1:1	<1.7:1	<1.7:1	<2.3:1	<2.3:1
VSWR (Max)	<3.0:1	<3.0:1	<3.0:1	<3.0:1	<3.0:1	<3.0:1	<3.0:1	<3.0:1
Peak Gain dBi (Typ)								
On Metal Housing*	2.1	0.7	1.7	5.4	4.6	4.5	3.4	3.7
On Plastic Housing w/ Ground Plane Kit	2.4	1.1	2.3	5.5	4.4	4.0	3.8	3.8
Peak Gain dBi (Max)								
On Metal Housing	2.5	1.1	2.3	5.9	4.8	4.9	3.8	4.0
On Plastic Housing w/ Ground Plane Kit	2.9	1.4	3.1	5.9	5.3	4.3	4.4	4.3
Nominal Impedence	50							
Max Power - ambient temp 25°C	10							
Polarization	Linear, Vertical							
Azimuth Beamwidth	Omnidirectional							

* Requires a 300-millimeter diameter ground plane kit (order separately with P/N HKIT-LPx-001)

MECHANICAL SPECIFICATIONS	
Dimensions – diameter x height – mm (inches)	Ø127 x 31 (Ø5 x 1.22)
Weight – kg (lbs.)	Approximately 0.2 (0.44)
Cable Type	RG316
Radome Material and Color	PC, UV stable, UL94-V0- material, black


ENVIRONMENTAL SPECIFICATIONS	
Operating Environment	Indoor or outdoor
Operating Temperature – °C (°F)	-30 to +70°C (-22 to +158°F)
Storage Temperature – °C (°F)	-40 to +85°C (-40 to +185°F)
Ingress Protection Rating	IP67
Material Substance Compliance	RoHS

MOUNTING




A threaded post on the back of the antenna and a supplied mounting nut is the primary mounting method when access is available to both sides of the mounting surface, such as a ceiling of a truck, meter, and vending machine. Mark the desired mounting location on the tile and cut a $\varnothing 20$ mm (0.8") hole for threaded post. Feed the cables through the hole and secure the antenna with the mounting nut.

The included rubber locking gasket should only be used with the mounting nut when mounting to a hard surface.

Note: You should mount the antenna on the desired location before you connect the cable. This ensures that you do not twist or damage the cable during the mounting of the antenna.





HOUSING CONFIGURATIONS



OPTIONAL GROUND PLANE KIT


For mounting on a non-metallic surface - Hardware Kit Part Number: HKIT-LPx-001




RADIATION PATTERNS

— On metal housing
— On plastic housing with ground plane kit


698 MHZ




880 MHZ




960 MHZ




1710 MHZ




1950 MHZ



2170 MHZ



2700 MHZ



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

08/25 Original