







Rating		16A 125VAC 1/3HP				
		10A 250VAC 1/2HP				
		10(4)A 250V~10E3				
		10A 125VAC,6A 250VAC CQC				
Contact Resistance	50m ohm Max.					
Insulation Resistance	DC 500V 100M ohm Min.					
Dielectric Strength	AC 1500V 1 minute					
Operation Temperature	-25°C~85°C	Thickness	X	Y		
Switch Function	3P SPDT ON-ON	0.75...1.25	19.2-0.1	13+0.1		
		1.25...2	19.4-0.1	13+0.1		
		2...3	19.8-0.1	13+0.1		



MATERIAL:
Frame: Black, Nylon#66
Actuator: Black, Nylon#66
Printed: None



Tolerances ±0.3 Unless Otherwise Specified

01/19/16	何坤	更新本體刻字及Rating,增加SCI Logo.				△
Date	Name	Description				No.
Drawn	Checked	Approved	SCI BOM No.	1820382	Model Name	ROCKER SWITCH
何坤	周木輝	研發部 李元生	Customer No.	112-R13-66C-B	Model No.	R13-66C-02
01/19/16	1/20-16	李元生	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 1