



H G F E D C B A

A.3; Valid é

ØB Max



1: COUPLING NUT



2: SHELL



SCALE 2/1

COUPE A-A

PLATING	1 : Coupling Nut	2 : Shell
A	Black anodized	
G	Olive drab cadmium (thickness 12 µ (-6/+10))	
J	Yellow cadmium	
N	Nickel	
R	Blue anodized	Black anodized
W	Olive drab cadmium (thickness 16 µ)	

SHELL SIZE	A Max	ØB Max	Mass (g) (±10%)
08	12.85	15.67	3.05
10		18.64	3.90
12		21.79	5.00
14		24.99	6.00
16		28.24	6.90
18		30.94	7.85
20		34.16	8.90
22		37.29	9.70
24		40.46	11.00

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

BASIC SERIES	852	01	R	08
BACKSHELL TYPE:	01 : Backnut			
PLATING:	A, G, J, N, R, W (see plating table)			
SHELL SIZE:	08, 10, 12, 14, 16, 18, 20, 22, 24			

Country	Jurisdiction & Control List
FR	NOT LISTED

P/N : SEE TABLE

A	21/12/2017	First issue		--
ISS	DATE	Latest modification - by: Q.LEBRETON		MOD N°
Designed by: Q.LEBRETON Date:21/12/2017		CUSTOMER DRAWING		
TITLE		BACKNUT SIZE 08 TO 24 852 SERIES		
Scale	3/1		General Linear Tolerances: ± 0.3	NPRDS / PROJECT 852
SOURIAU		WWW.SOURIAU.COM		This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT	A3	SOURIAU DRG N° C023-J852-A		
				SHEET 1 / 1