

CH-W-S-A22-P7.5-V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Wallbox, With attached 7.5 m cable and type 2 plug, Mobile App, RFID/NFC
Order No.	2911260000
Type	CH-W-S-A22-P7.5-V
GTIN (EAN)	4099986532236
Qty.	1 pc(s).

CH-W-S-A22-P7.5-V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	149 mm	Depth (inches)	5.866 inch
Height	439 mm	Height (inches)	17.283 inch
Width	273 mm	Width (inches)	10.748 inch
Net weight	7,274 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-30 °C...50 °C
Operating temperature, min.	-30 °C	Operating temperature, max.	50 °C

Material data

Max. relative humidity during storage	95 %	Operating temperature, max.	50 °C
Operating temperature, min.	-30 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C		

Performance specification

Performance specification	Input voltage type	AC
	Input voltage	400 V
	Input current, max.	32 A
	Charging power, max	22 kW
	Adjustment accuracy	1 A
	Charging current adjustable	Yes
	Charging current, min	6 A

System requirements

Connection system	With attached 7.5 m cable and type 2 plug	Type of communication to vehicle	Control Pilot (CP), Proximity Pilot / Plug Present (PP)
Charge mode	Mode 3	Protection class	I
Surge voltage category	III	Pollution severity	3

Features

Protection degree	IP54	Type of status indicator	RGB LED
Welding detection	Yes	Failure shutdown	Yes
Failure shutdown method	All-pole	DC - residual current detection integrated	Yes
DC - residual current	6 mA	Type of residual current detection to be provided by the installation	RCD Type A
User authentication	Yes	Mobile App available	Yes
User authentication type	Mobile App, RFID/NFC	Energy measurement integrated	Yes
Integrated energy measuring MID conform	Yes	Load management integrated	Yes
Load management type	static	Communication integrated	Yes
Supported protocols	Modbus RTU, Modbus TCP, OCPP 1.6 (J)		

CH-W-S-A22-P7.5-V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Interfaces**

Wifi frequency	2,4 GHz	Wifi Standard	802.11 b/g/n
Bluetooth module	Bluetooth Low Energy (BLE)	Ethernet ports	2
Digital inputs	5 (12 V / 6 mA)	Digital outputs	1 (12 V / 100 mA)
Type of protocol of serial interface	RS485		

Assembly

Installation	Wall mounting, Stand Mounting
--------------	-------------------------------

Included in delivery

Included in delivery	Drilling template, Instruction sheet, 5 RFID-transponder, Mounting screws, Assembly dowels, cover
----------------------	---

Housing

Operating altitude	≤ 3000 m	Housing main material	PC
Protection degree	IP54	Colour	black, Anthracite, grey
Impact resistance	IK10 in accordance with IEC 62262		

Approvals and norms

Approvals	IEC 61851-1, IEC 61851-21-2, IEC 62196-1, IEC 62196-2, EN 50620, EN 301 489-1, EN 301 908-1, EN 301 511, EN 300 328, EN 300 330 v.2.1.1, EN 62368-1, EN 55011
-----------	---

Connection data (supply cable)

Conductor cross-section, max.	16 mm ²
-------------------------------	--------------------

Classifications

ETIM 6.0	EC002883	ETIM 7.0	EC002883
ETIM 8.0	EC002883	ECLASS 9.0	27-14-47-01
ECLASS 9.1	27-14-47-01	ECLASS 10.0	27-14-47-01
ECLASS 11.0	27-14-47-01	ECLASS 12.0	27-14-47-01

CH-W-S-A22-P7.5-V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**Approval/Certificate/Document of
Conformity[CE declaration](#)

Engineering Data

[Installationsvideo AC SMART](#)[Installation Video AC SMART](#)[AC SMART Modbus registers](#)

Software

[Firmware – Current Bluetooth Firmware AC SMART](#)[Firmware – Current Firmware AC SMART](#)[Firmware – Current WiFi Firmware AC SMART](#)[Firmware – Archive Firmware files AC SMART](#)[Firmware – Release notes Current firmware AC SMART](#)

Tender specification

[Ausschreibungstexte](#)

User Documentation

[Broschüre Wallbox AC SMART, AC Ladekabel, Basiskomponenten](#)[Brochure EV charging box AC SMART, AC charging cables, Basic components](#)[Abnahmeprotokoll AC SMART](#)[MANUAL AC SMART \(DE, EN\)](#)[Application notes – Instructionsheet AC SMART](#)

Catalogues

[Catalogues in PDF-format](#)

CH-W-S-A22-P7.5-V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

