



REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
F	REVISED & REDRAWN PER E.O. 69421	11/9/71	<i>Boyle</i>

F 75700-*****P/S



SHELL SIZE	A MAX.	B MAX.	C MAX.
2	1.316	.417	1.016
3	1.957	.417	1.657
4	1.957	.497	1.657
6	1.957	.658	1.657
7	2.430	.658	2.130



- THIS DRAWING APPLIES TO THOSE ARRANGEMENTS WITH ONLY SIZE 22 CONTACT CAVITIES.
- CONTACT SPACING .080 CENTER TO CENTER
- JACKSCREW ACTUATED BY 5/32" HEXAGON KEY WRENCH. JACK RECEPTACLE TO HAVE #6-32 PAN HEAD SCREW.
- WIRE ACCOMMODATIONS, CONDUCTOR SIZE AWG 22 THRU 26. REAR INSERTS SEAL ON SMOOTH INSULATION OF .033 MIN. TO .054 MAX.
- FOR CONTACT ARRANGEMENTS SEE CATALOG PAGE 75500.
- SEE "GENERAL DESCRIPTION" FOR ELECTRICAL AND MATERIAL SPECIFICATIONS.

NOTE:

SIGNATURE & DATE		CP		MATERIAL	
DR	<i>H. J. Jernstedt</i> 11-9-71	CP	<i>H</i>	MATL	<i>H</i>
CHK	<i>G. King</i> 11-9-71	The Deutsch Company ELECTRONIC COMPONENTS DIVISION Municipal Airport Banning, California			
PE	<i>Boyle</i> 11-9-71				
APPD					
SCALE NONE		WT <i>H</i>		SHEET 1 OF 1	

CONNECTOR, PLUG/RECEPTACLE RECTANGULAR, SUBMINIATURE, METAL SHELL AND CABLE CLAMP, JACKSCREW COUPLING, REAR INSERTION & REMOVAL, -ENVELOPE-

B	75700-***** P/S
DWG SIZE	CODE 11139