

14NOV2017 nberger	 TE Connectivity			
14NOV2017 de Burgt				
14NOV2017 nrethlinder	NAME SUBASSEMBLY SOCKET CONTACT			
SPEC	MATE-AX 180 DEGREES, RG174			
94515				
ION SPEC				
				
0.45g	SIZE A	CAGE CODE -	DRAWING NO C=2298494	RESTRICTED TO
ER DRAWING			SCALE 10:1	SHEET 1 OF 1
			REV A3	



- | | |
|---|---|
| 1 | PACKAGING: PRODUCT REELED ON CORRUGATED REEL WITH INTERLEAVING PAPER
Verpackung: Spulenware auf Wellpappespule mit Zwischenlagenpapier |
| 2 | CONDITION AS DELIVERED
Auslieferungszustand |



- REVISION STATE AND DATE CODE
Revisionstatus und Datumscode

- LISTED WEIGHT INCLUDE THE CARRIER STRIP AND THE DIELECTRIC
Gewicht inklusive Trägerstreifen und Dielektrikum

- APPLICATION TOOL PN SEE IN APPLICATION SPEC, 114-94413
PN des Applicators siehe in Verarbeitungsspec. 114-94413.

- ALLOWED AREA FOR CONTACT GRIPPING FOR CABLE TERMINATION
Zulaessiger Bereich zum Greifen des kontaktes bei der Kabelverarbeitung

- DURING PROCESSES, THE CONTACT MAY BE LOADED WITH
MAX. 30N IN AXIAL DIRECTION
Bei der Verarbeitung darf der Kontakt an gezeigter Stelle
axial mit max. 30N belastet werden

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14NOV2017 K.Weinberger		 TE Connectivity	
DIMENSIONS:		CkW 14NOV2017 G.van de Burgt			
mm		APVD 14NOV2017 C.Schreittlinger		NAME	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SUBASSEMBLY SOCKET CONTACT	
				MATE-AX 180 DEGREES, RG174	
MATERIAL		FINISH		PRODUCT SPEC	
				108-94515	
				APPLICATION SPEC	
					
		WEIGHT		SIZE	
		 0.45g		CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
		CUSTOMER DRAWING		 -  2298494	
				SCALE	
				10:1	
				SHEET	
				1 of 1	
				REV	
				A3	

