

NOTES:

Materials: SST. corrosion-resistant, Non Magnetic 303, per ASTM A484 and A582. Beryllium Copper per ASTM-B-196, QQ-C-530 Oxide-Noryl (tm), MIL-P-46129



Finish: Center Conductors and solder components shall be plated per MIL-G-45204 Type II, Class 1 over Nickel plate per QQ-N-290. Body and Body components shall be passivated per ASTM A380.

Frequency: DC-40 GHz

VSWR: 1.25 TO 40 GHz

Insertion Loss: $.05\sqrt{\text{Frequency}}$

25-130-1500-90



LTR	DESCRIPTION	DATE	APPR.	DRAWN	CHECKED	USED ON	Σ SRI CONNECTOR GAGE CO. 3950 DOW ROAD MELBOURNE FL. 32934	
—	REL	04/03		APPR.	SCALE	25-130-1500-90		
				UNLESS OTHERWISE SPECIFIED: 1. REMOVE ALL BURRS 2. BREAK ALL CORNERS & EDGES .005 R. MAX 3. CHAMFER 1st & LAST THREADS 45° 4. SURFACE FINISHED 32/ UNLESS OTHERWISE SPECIFIED. 5. DIAMETERS ON COMMON CENTERS TO BE CONCENTRIC WITHIN .002 T.I.R. 6. ALL DIMENSIONS ARE AFTER PLATING.			MATERIAL	TITLE
							FINISH	2.9mm JACK 2 HOLE FLANGE
				DIMENSIONS ARE IN INCHES TOLERANCES			SIZE	FSCM NO.
							A	OHMO1
				DECIMALS .X ±.030 .XX ±.010 .XXX +.005	FRACTIONAL ± 1/64	ANGULAR .X° ±1°0' .X°X' ±15'	SHEET 1	DWG. NO. 25-130-1500-90