


This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.

REV	DESCRIPTION	DATE	APRD
B	CORRECT BEAD MATERIAL ER076415	02/08/2019	ASNZ

NOTES:
MATERIAL:
STAINLESS STEEL 303 PER ASTM A582
BERYLLUM COPPER PER ASTM-B-196
OXIDE NORYL

FINISH:
CENTER CONDUCTORS AND SOLDER COMPONENTS SHALL BE GOLD PLATED ER MIL-G-45204
TYPE II, CLASS 1 OVER NICKEL PLATE PR QQ-N-290.
BODY AND BODY COMPONENTS SHALL BE PASSIVATED PER AMS 2700.

ELECTRICAL CHARACTERISTICS:
FREQUENCY: DC-40 GHz
VSWR: 1.3:1 TO 40 GHz



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
.X: ± 0.030
.XX: ± 0.010
.XXX: ± 0.005
ANGLES: X*: $\pm 1^\circ$
X*X*: $\pm 15^\circ$
MACHINED SURFACES:
32/

DRAWN FAA	DATE 7/14	 245 Lynnfield St. Peabody, MA 01960	
APPR.	DATE		
APPR.	DATE	TITLE: 2.4 mm PLUG TO 2.9 mm PLUG	
dcamelio		SIZE B	DWG. NO. 26-924-0000-91
THIRD ANGLE PROJECTION 		SH 1 OF 1	REV B