

This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.

REV.	DESCRIPTION	DATE	APPROVED
A	ER077068	04/03/19	MAR

NOTES:

1. MATERIAL SPECIFICATIONS:

STAINLESS STEEL, S30300, PER ASTM A582.
BERYLLIUM COPPER PER ASTM B196.
OXIDE-NOYRL (fm) PER MIL-P-46129.

2. FINISH SPECIFICATIONS:



BODIES: PASSIVATED PER ASTM A380.
CONTACT: GOLD PER MIL-G-45204, TYPE II, CLASS 1 OVER
NICKEL PER QQ-N-290.

3. ELECTRICAL SPECIFICATIONS:

FREQUENCY RANGE: DC - 50 GHz.
VSWR: 1.4:1 MAX. PRODUCT ONLY,
NO LOAD OR TEST ADAPTER IN MEASUREMENT.

4. MECHANICAL SPECIFICATIONS:

DURABILITY: 500 CYCLES MINIMUM.
RECOMMENDED MATING TORQUE: 8 - 10 IN-LBS.
CONNECTOR MEETS GENERAL ELECTRICAL,
MECHANICAL, AND ENVIRONMENTAL
REQUIREMENTS OF MIL-PRF-39012 AND MIL-STD-348B.



CATALOG PART NUMBER: 26-927-2010-41

 **Winchester**
Interconnect

245 Lynnfield St.
Peabody, MA 01960

DRAWN LMW	DATE 04/18	APPR.	DATE	TITLE: 2.4 MM PLUG TO 2.4 MM JACK RIGHT ANGLE ADAPTER
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES				
TOLERANCES: X: ±0.1 XX: ±0.01 XXX: ±0.005 ANGLES: ±1.0° MACHINED SURFACES:				SIZE B DWG. NO. 26-927-2010-41C REV A SH 1 OF 1