

This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.

REV.	DESCRIPTION	DATE	APPROVED
A	ECO-14834	2/21/2022	ASNZ

NOTES:

MATERIALS:




STAINLESS STEEL PER ASTM A582.
BERYLLIUM COPPER PR ASTM B196.
OXIDE NORYL (tm), MIL-P-46129.

FINISH:

CENTER CONDUCTORS SHALL BE GOLD PLATED PER MIL-DTL-45204D.
TYPE II, CLASS 1 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290.
BODY AND BODY COMPONENT SHALL BE PASSIVATED PER ASTM A380.

ELECTRICALS:

NOMINAL IMPEDANCE: 50 OHMS.
FREQUENCY RANGE: DC - 18 GHz.
VSWR: 1.15: 1 MAX TO 18 GHz (PRODUCT ONLY).
INSERTION LOSS: .05 $\sqrt{F}$ (GHz) dB.



245 Lynnfield St.
Peabody, MA 01960

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
.X: ± 0.1
.XX: ± 0.01
.XXX: ± 0.005
ANGLES: $\pm 1.0^\circ$
MACHINED SURFACES:
63/

DRAWN LRH	DATE 10/99	 Winchester Interconnect _{LLC}	245 Lynnfield St. Peabody, MA 01960	
APPR.	DATE			
APPR.	DATE	TITLE: TYPE N PLUG TO 3.5 mm PLUG ADAPTER		
dcamelio				
THIRD ANGLE PROJECTION 		SIZE B	DWG. NO. 52-922-0000-70	REV A
		SH 1 OF 1		

DOC. REV.