

This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.

REV	DESCRIPTION	DATE	APRD
A	CORRECT MATERIAL USED ER076128	01/25/2019	ASNZ

NOTES:

MATERIALS:

STAINLESS STEEL 303 PER ASTM A484 AND A582.
BERYLLIUM COPPER PER ASTM-B-196, QQ-C-530.
PTFE

FINISH:

CENTER CONDUCTORS AND SOLDER COMPONENTS SHALL BE PER MIL-5-G-45204
TYPE II, CLASS 1 OVER NICKEL PLATE PER QQ-N-290.
BODY AND BODY COMPONENTS SHALL BE PASSIVATED PER ASTM A380.

FREQUENCY:


DC-18 GHz

VSWR:

1.15 TO 18 GHz

INSERTION LOSS:

.05√F(GHz)



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES

TOLERANCES:
.X: ±0.030
.XX: ±0.010
.XXX: ±0.005
ANGLES: X°: ±1°
X°X': ±15'
MACHINED SURFACES:

32/

DRAWN LRH	DATE 02/01	 Winchester Interconnect. 245 Lynnfield St. Peabody, MA 01960	
APPR.	DATE		
APPR.	DATE	TITLE: N PLUG TO 2.9 mm JACK	
dcamelio		SIZE B	DWG. NO. 52-925-0003-70
THIRD ANGLE PROJECTION 		SH 1 OF 1	REV A

DOC. REV.