

This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.

REV	DESCRIPTION	DATE	APRD
A	REDRAW TO CAD ONLY ER074649	8/31/2018	ASNZ

NOTE:
MATERIAL:

STAINLESS STEEL 303, PER ASTM A484 AND A582
BERYLLIUM COPPER PER ASTM-B-196, QQ-C-530
OXYDE-NORYL (tm), MIL-P-46129.

FINISH:

CENTER CONDUCTORS AND SOLDER COMPONENTS SHALL BE PLATERD PER MIL-G-45204
TYPE II, CLASS 1 OVER NICKEL PLATE PER QQ-N-290.
BODY AND BODY SHALL BE PASSIVATED PER ASTM A380.

FREQUENCY:


DC-50 GHz

VSWR:

1.4 TO 50 GHz

INSERTION LOSS:

.05√FREQUENCY



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
.X: ±0.030
.XX: ±0.015
XXX: ±0.005
ANGLES: X°: ±1°
X°X': ±15'
FRACTIONAL: 1/64
MACHINED SURFACES:
63/

DRAWN FAA	DATE 01/14	 Winchester Interconnect 245 Lynnfield St. Peabody, MA 01960	
APPR.	DATE		
APPR.	DATE	TITLE: 1.85 mm PLUG TO 2.4 mm JACK, RIGHT ANGLE ADAPTER	
dcamelio		SIZE B	DWG. NO. 84-927-2010-40
THIRD ANGLE PROJECTION 		SH 1 OF 1	REV A

DOC. REV.]