


DASH NO.	M CODE	MADE FROM
----------	--------	-----------



NOTES:

- FOR USE WITH RG-58, 58A & 58C/U CABLE.
- FOR CABLING INSTRUCTIONS SEE 3-7-1.
- FOR CRIMPING USE DIE KTH-2001.
- MATERIALS:
 INSULATOR: HIGH DENSITY POLYETHYLENE, ASTM-D4976
 GASKET: SILICONE RUBBER, A-A-59588
 HEAT SHRINK TUBING: POLYOLEFIN, PER MIL-I-23053/5 COLOR: WHITE
 K-GRIP SLEEVE: COM. BRONZE, ASTM-B-135
 K-GRIP BODY: BRASS, ASTM-B16
 WASHERS: BRASS, ASTM-B16
 ALL OTHER METAL PARTS: BER. COPPER, ASTM-B-196
- FINISHES:
 CENTER CONTACT: HARD GOLD PLATE, PER ASTM-B488
 SPRING WASHER: SILVER PLATE, PER ASTM-B700
 ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT NICKEL FINISH (TR-5)
- ELECTRICAL CHARACTERISTICS:
 WORKING VOLTAGE: 10 KV DC
- DIMENSIONS IN INCHES [MM].

UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES [MILLIMETERS].
- TOLERANCES:
 .XXX ±.004 .XX ±.010
 [.XXX ±.10] [.XX ±.25]
 FRACTIONS: X/Y ±.010 [.25] ANGLES: ± 1°
 ★ CRITICAL DIMENSIONS

REVISIONS

ISSUE	CHANGES
13	CN 33334 E REDRAWN WJM 08/26/91
14	CN 37544 C KH 02/20/98
15	CN 38562 E TML 05/28/02
16	CN 39736 C DCT 12/18/06
U	ER 7276 DCT 5/4/8

1065-1QD

CUSTOMER
SALES DRAW

SCALE 4:1

APPROX SURFACE AREA

USED ON

REF:

PLUG. 10KV

DRAWN MJB	DATE 08/26/61
DESIGN MJB	DATE 09/04/61
APPR.	DATE

1065-1QD