





NOTES:

1. INTERFACE PER MIL-STD-348, FIG. 301-1.
2. SAME AS UG-911 A/U EXCEPT FOR FINISH.
3. MATERIALS:
INSULATOR: TEFLON, ASTM-D-1457
GASKET: SILICONE RUBBER, ZZ-R-765
CENTER CONTACT: BER. COP., ASTM-B-196
LOCKWASHER: PHOS. BRONZE, QQ-B-750
ALL OTHER METAL PARTS: BRASS, ASTM-B16
4. FINISHES:
CENTER CONTACT: SILVER PLATE PER QQ-S-365
GLASS SEAL: TIN DIPPED
ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT FINISH (TR-5)
5. ELECTRICAL CHARACTERISTICS:
NOMINAL IMPEDANCE: 50 OHMS
VOLTAGE RATING: 500 VRMS
FREQUENCY RANGE: DC TO 4
6. ENVIRONMENTAL:
LEAKAGE RATE SHALL NOT EXCEED 1×10^{-7} cc/sec OF
TRACER GAS AT ATMOSPHERIC PRESSURE.

REVISIONS

ISSUE	CHANGES
0	ER 6183 JM 07/22/68
1	CN 6188 A JM 07/23/68
2	CN 18605 C MA 09/22/78
3	CN 37587 C REDRAWN TML 10/13/99
E	REVISED PER ER23475 GGR 04/23/2010

KC7974S

CUSTOMER SALES DRAWING

SCALE 4:1

APPROX SURFACE AREA

USED ON

REF:

RECEPTACLE, BULKHEAD,
HERMETIC SEAL, BNC

DRAWN MZB	DATE 11/03/88
DESIGN MJB	DATE 11/15/88
APPR.	DATE

KINGS
by WINCHESTER
ELECTRONICS

Winchester Electronics
62 Barnes Industrial
Road North
Wallingford, CT 06492

SDKC-79-74