


NOTES:

1. FOR USE WITH COMMSCOPE 77538 & BELDEN 1855A & 1865A CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-661-1.
3. FOR CRIMPING USE DIE KTH-2025.
4. CENTER CONTACT, 1-6690-7M9Y, AND K-GRIP SLEEVE 1-33983-1M06 SUPPLIED UNASSEMBLED.
5. INTERFACE PER MIL-STD-348, FIG. 301-1 (AS APPLICABLE).
6. MATERIAL SPECIFICATIONS:
INSULATOR: PTFE PER ASTM D4894.
GASKET: SILICONE RUBBER PER ZZ-R765.
SPRING WASHER AND OUTER CONTACT: BERYLLIUM COPPER PER ASTM B196.
ALL OTHER METAL PARTS: BRASS PER ASTM B16.
7. FINISH SPECIFICATIONS:
CENTER CONTACT: GOLD PER MIL-G-45204
SPRING WASHER: SILVER PER QQ-S-365
ALL OTHER METAL PARTS: NICKEL PER QQ-N-290

8. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 75 OHMS
WORKING VOLTAGE: 500 VOLTS RMS
FREQUENCY RANGE: DC - 12 GHz
RETURN LOSS: -30dB MAX TO 3.0 GHz
-20dB MAX TO 6.0 GHz
9. COMPLIANT TO 3G/6G/12G SDI SMPTE REQUIREMENTS.
10. MARK PACKAGE: KINGS 2065-11-9.

REV	DESCRIPTION	BY	DATE	APPD
K	ER066126	J	12/20/16	DCAM



CATALOG P/N: 2065-11-9

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.3] XXX [XXX] ± .005 [0.13] XXXX [XXXX] ± .000X ANGLES: ± 2° SCALE: 4:1				 by WINCHESTER Winchester Electronics Corporation 199 Park Road Ext Suite 104 Middlebury, Connecticut 06762				
CUSTOMER SALES DRAWING				 THIRD ANGLE		75 OHM BNC PLUG FOR BELDEN 1855A OR EQUIVALENT CABLE (ROHS)		
DRAWN J	DATE 04/09/2015	APPROVED MAR	DATE 07/28/2015	A	SD2065-11-9	SHT 1	OF 1	REV K
APPROVED YA	DATE 04/09/2015	APPROVED XXX	DATE XX/XX/XX					