




This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.

REV	DESCRIPTION	DATE	APPD
E	ECO-13334	02/02/2021	LA



5	CRAB FOOT	1	STEEL	NICKEL	MATERIAL SEE TABLE	DO NOT SCALE DRAWING	DRAWN LA	DATE 02/02/2021	 Winchester Interconnect. 245 Lynnfield St, Peabody, MA 01960			
4	PRESS FIT WASHER	1	BRASS	NICKEL		UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS	ENG APPR. LA	DATE 02/02/2021				
3	INSULATOR	1	PTFE	NATURAL		TOLERANCES: FRACTIONS: ± 1/64 .XX : ±.01 .XXX: ±.005 ANGLES: ± 1/2' MACHINED SURFACES:	MFG APPR.	DATE				
2	PIN	1	BRASS	GOLD		COMMENTS:	OTHER APPR.	DATE	TITLE: BNC V-BITE JACK			
1	BODY	1	BRASS	NICKEL			THIRD ANGLE PROJECTION 					
NO	DESCRIPTION	QTY	MATERIAL	FINISH	surface area: sq inch	weight: 8.681 lbs	SIZE B		DWG. NO. 361V504ER		REV E	
							PER ASME Y14.5M-1994		SCALE: 5:1		SHEET 1 OF 1	