



NOTES: UNLESS OTHERWISE SPECIFIED

1. FOR USE WITH RG-58, 58A, 58C, 141 & 141A/U CABLE.
2. MATERIALS:
 INSULATOR: PTFE, ASTM D1710
 GASKETS: SILICONE RUBBER: ZZ-R-765
 FERRULE: COM. BRONZE TUBE ASTM B135
 OUTER CONTACT, CENTER CONTACT & SPRING CONTACT: BERYLLIUM COPPER UNS C17300, PER ASTM B196
 ALL OTHER METAL PARTS: BRASS PER ASTM B16
3. FINISHES:
 CONTACT: .000050 MIN. GOLD OVER .000050 MIN. NICKEL (RoHS)
 SPRING WASHER: .000200 MIN THICK SILVER OVER .000020 MIN THICK COPPER (RoHS)
 ALL METAL PARTS: .000050 MIN THICK NICKEL OVER .000050 MIN THICK COPPER (RoHS)
4. FOR CABLING INSTRUCTIONS SEE CP-441
5. FOR CABLE TRIMMING USE KTJ-72 & KTO-136
6. FOR CRIMPING USE KTH-2061
7. ELECTRICAL CHARACTERISTICS:
 OPERATING VOLTAGE: 3500 VOLTS AC
 5000 VOLTS DC

REV	DESCRIPTION	BY DATE	APPD
A	RELEASED ER058664	DCam 6/3/15	GM



CATALOG P/N: 1705R-2

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [X.X] $\pm .01$ [0.3] .XXX [X.XX] $\pm .005$ [0.13] .XXXX [X.XXX] $\pm .XXXX$ ANGLES: $\pm 2^\circ$ SCALE: 3:1				WINCHESTER ELECTRONICS Winchester Electronics Corporation 62 Barnes Industrial Road North Wallingford, Connecticut 06492			
CUSTOMER SALES DRAWING				THIRD ANGLE			
DRAWN	DATE	APPROVED	DATE	PLUG, SHV (RoHS COMPLIANT)			
CY	05/07/15	DCam	05/08/15				
APPROVED	DATE	APPROVED	DATE				
PL	6/3/15	TH	6/3/15				
A				SD1705R-2		SHT OF	REV
						1 1	A